

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Universal, 5-position, Socket, straight, M8, B-coding, SMD reflow, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1412222
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB22
Product key	ABQHCS
GTIN	4046356988315
Weight per piece (including packing)	2.94 g
Weight per piece (excluding packing)	2.16 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Data, signals
Sensor type	Universal
Number of positions	5
Seal present	no
Shielded	no
Coding	B
Thread type	M8

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\leq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC 30 V DC
Nominal current I_N	3 A

Connection data

Connection method	SMD reflow
-------------------	------------

Interfaces

Bus system	DeviceNet™
Signal type/category	Universal

Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

Connector

Connection 1

SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	B

Cable/line

Signal type/category	Universal
----------------------	-----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C (Plug / socket)
	-55 °C ... 105 °C (without mechanical actuation)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

Packaging specifications

Type of packaging	Tray
-------------------	------

SACC-CI-M8FSB-5P SMD T - Contact carrier


1412222

<https://www.phoenixcontact.com/us/products/1412222>



Drawings

Schematic diagram



Pin assignment of M8 socket, 5-pos., B-coded

SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412222>

 cULus Recognized Approval ID: E221474-20160506				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	3 A	-	-

SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7ee4087b-74e5-4efd-9eda-27f1980f66ff

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com