



EE-SPX303N

Photomicro sensor, slot type, 13 mm, D-ON, NPN, connector

Specifications

Shape	Straight
Sensing method	Through-beam with slot
Sensing distance	13 mm
Setting method	Fixed
Connection method	System connector
Output type	NPN
Operation mode	Dark-ON
Response time	5 ms
Material housing	Polycarbonate
Thread size	Other
Product Width (unpacked)	26 mm
Product Height (unpacked)	26 mm
Product Depth (unpacked)	7.4 mm
Type of light	Infrared light
Supply voltage DC	12-24 V

Accessories

	EE-1001	Accessory Connector for Photomicrosensors, 4-pin , solder terminals
	EE-1001-1	Connector for Photomicrosensors, 4-pin , solder terminals, bridge between L and +
	EE-1010 2M	Accessory Photomicro sensor EE-SPX_03, cable connector, PVC, 2m
	EE-1010-R 2M	Accessory photomicro sensor EE-SPX_03, cable connector, robotic PVC, 2 m
	EE-2002	Accessory Photomicro sensor EE-SPX_03, NPN/PNP converter and cable connector, 0.5 m

Downloads

CAD Library



**EE-SPX303N/403N
Broad Slot-type
Photomicrosensor**
Datasheet

EN PDF 663 KB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 14 August, 2025. Click here for [terms of use](#).



INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](#)