







SECTION A-A



P.C.B. Layout



Revision:	Date:	Description:	Prepared:	Notes:	<div>TENSILITY</div> <div> tel 1.541.323.3228 800 877.670.7118  fax 1.541.323.4202 web tensility.com </div>		
A	9/26/2018	Initial release	Verified:				
			Dimensions are in millimeters. Tolerances: < 1.0: ± 0.1 mm 1.0 to 10.0: ± 0.2 mm > 10.0: ± 0.3 mm	Description:	Size:	Part number:	
				Connector, dc jack 2.35x0.7 mm, PCB mount, 90°, silver plated, thru hole	A	54-00138	
					Scale: 5:1		Sheet 1 of 2

5

↑

4

3

2

1

