Part Number : 1731070060
Product Description : FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell, 7 Circuits Max, 5 Signal Contacts Loaded, Green Insulator
Series Number : 173107
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : FM7W2S-K121



Documents and Resources

Drawings

1731070060_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:8b8d0517-a3cc-4fe0-9b46-033306fe32c6
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell, 7 Circuits Max, 5 Signal Contacts Loaded, Green Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056316996

Electrical

Current - Maximum per Contact	7.5A
Shielded	Yes

Physical

Circuits (Loaded)	5
Circuits (maximum)	7
Color - Resin	Green
Durability (mating cycles min)	500
Gender	Female

Downloaded from Arrow.com.

Material - Contact	Copper Alloy
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Shell	Steel
Net Weight	6.700/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Flange
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shell Size	2
Temperature Range - Operating	-55° to +130°C
Termination Style	Solder Cup
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Wire Size (AWG)	20

Mates With / Use With

Mates with Part(s)

Description	Part Number
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 7 Circuits Max, 5 Signal Contacts Loaded, Green Insulator	1731070059

Downloaded from Arrow.com.

Use with Part(s)

Description	Part Number
FCT High Power Contact, Female, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 40.0A, 18-2 AWG	1727040156
FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 40.0A, 10-8 AWG	1727040153
FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 14-12 AWG,	1727040151
FCT High Power Contact, Female, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 16-12 AWG	1727040155
FCT High Voltage Contact, Female, Straight, Solder Cup, 1.30µm Gold Mating Plating, with Plastic Retention Clip, 2.0A, 20 AWG or smaller	1727040135
FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 10.0A, 20-16 AWG	1727040150
FCT High Power Contact, Female, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 10.0A, 20-16 AWG	1727040154
FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 30.0A, 12-10 AWG	1727040157
FCT High Power Contact, Female,	1731120391

Downloaded from Arrow.com.

Straight, Solder Cup, 1.30µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 40.0A, 18-2 AWG	
FCT Coaxial Contact, Female, Straight, Crimp, 50 Ohms, 1.30µm Gold Plating, for RG-316U Double Braided Cable	1731120053
FCT High Voltage Contact, Female, Right-Angle, Solder Cup, 1.30µm Gold Mating Plating, with Plastic Retention Clip, 2.0A, 20 AWG or smaller	1731120031
FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 14-12 AWG,	1731120326
FCT Coaxial Contact, Female, Straight, Solder Cable Termination, 50 Ohms, 1.30µm Gold Plating, without Inspection Hole, for RG-174U, RG-188AU, or RG-316U Cable	1727040133

Downloaded from Arrow.com.