

T4162214004-005

RPC-M12-4MR-5.0SH-M12-4FR-PVC




TE Internal #: **T4162214004-005**
TE Internal Description: **RPC-M12-4MR-5.0SH-M12-4FR-PVC**
[All M12 A-CODE MR-FR DOUBLE ENDED CABLE \(112\)](#)

Connector Type : **Plug/Receptacle**
Number of Positions : **4**
Keying : **A**
Housing Material : **GF Nylon**
Cable Assembly Type : **M12 to M12**

[Similar Products](#) | [Digital Datasheet](#)



Compatible Parts & Tooling



We are here to help!
Get in touch with our product experts.

 **CHAT WITH US**

 **EMAIL US**

 **CALL US**

Feedback

Documents	Features	Product Compliance
Product Description	M12 A-code Male R/A to Female R/A Assemblies are offered in 2 up to 5 positions PUR/PVC, Shielded & non-shielded, up to 10m length. View All M12 A-CODE MR-FR DOUBLE ENDED CABLE (112)	
Product Drawings	RPC-M12-4MR-5.0SH-M12-4FR-PVC RPC-M12-4MR-5.0SH-M12-4FR-PVC English	
CAD Files	3D PDF 3D_CVM_CVM_T4162214004-005_A.pdf 3D Customer View Model ENG_CVM_CVM_T4162214004-005_A.2d_dxf.zip English ENG_CVM_CVM_T4162214004-005_A.3d_igs.zip English ENG_CVM_CVM_T4162214004-005_A.3d_stp.zip English	
Datasheets & Catalog Pages	M8/M12 Sensor Actuator Cable Assemblies Datasheet ENG_DS_1-1773966-2_0119.pdf English	
Product Specifications	M12 screw connection application specification M12 screw connection application specification 4-137144_A2.pdf English	

Product Description

M12 A-code Male R/A to Female R/A Assemblies are offered in 2 up to 5 positions PUR/PVC, Shielded & non-shielded, up to 10m length.

[View All M12 A-CODE MR-FR DOUBLE ENDED CABLE \(112\)](#)

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Assembly Type : **Pigtail**
Connector Type : **Plug/Receptacle**
Cable Assembly Type : **M12 to M12**
Shielded : **Yes**
Cable Type : **PVC**
Product Type : **Cable Assembly**
LED : **Without**

Configuration Features

Number of Positions : **4**
Keying : **A**
Configuration : **Double Ended**

Electrical Characteristics

Operating Voltage (VDC): **250**
Operating Voltage (VAC): **250**

Body Features

Cable Jacket Color : **Black**
Insulation Material : **PVC**
Wire Color : **Brown, White, Blue, Black**
Connector Color : **Blue**
Conductor Material : **Copper Alloy**
Environmental Protection : **With**
Cable Exit Angle : **Right Angle**

Contact Features

Contact Current Rating (A): **4**

Mechanical Attachment

Screw & Hole Thread Size : **M12 x M12**

Housing Features

Housing Material : **GF Nylon**

Dimensions

Wire Size (mm²): **.34**
Wire Size (AWG): **22**
Cable Assembly Length (mm): **5000**

Operation/Application

M8/M12 Application Type : **Sensor/Actuator**



Other	Field Serviceable : Yes																																																
EU RoHS Directive 2011/65/EU	Exemptions: 6(c) - Pb-Alloy in Copper <i>This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).</i>																																																
EU ELV Directive 2000/53/EC																																																	
China RoHS 2 Directive MIIT Order No 32, 2016	<table><tr><th rowspan="2">部件名称 (Component Name) T4162214004-005</th><th colspan="6">有害物质 (Hazardous Substance)</th></tr><tr><th>铅 (Pb)</th><th>汞 (Hg)</th><th>镉 (Cd)</th><th>六价 铬 (Cr6)</th><th>多溴联 苯 (PBB)</th><th>多溴二苯 醚 (PBDE)</th></tr><tr><td>连接器系统 (Connector Systems)</td><td>X</td><td>○</td><td>○</td><td>○</td><td>○</td><td>○</td></tr><tr><td colspan="7">本表格依据SJ/T 11364标准的规定编制。This table is compiled according to SJ/T 11364 standard.</td></tr><tr><td colspan="7">○: 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572标准规定的限量要求以下。 Indicates that the concentration of the hazardous substance in all homogeneous materials of the part is below the relevant threshold of the GB/T 26572 standard.</td></tr><tr><td colspan="7">X: 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572标准规定的限量要求。 Indicates that the concentration of the hazardous substance in at least one homogeneous material of the part is above the relevant threshold of the GB/T 26572 standard.</td></tr><tr><td colspan="7">电子电气产品的环保使用期限依据SJ/T 11388标准的规定确定。 The EFUP value of EEP is defined according to SJ/T 11388 standard.</td></tr></table>	部件名称 (Component Name) T4162214004-005	有害物质 (Hazardous Substance)						铅 (Pb)	汞 (Hg)	镉 (Cd)	六价 铬 (Cr6)	多溴联 苯 (PBB)	多溴二苯 醚 (PBDE)	连接器系统 (Connector Systems)	X	○	○	○	○	○	本表格依据SJ/T 11364标准的规定编制。This table is compiled according to SJ/T 11364 standard.							○: 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572标准规定的限量要求以下。 Indicates that the concentration of the hazardous substance in all homogeneous materials of the part is below the relevant threshold of the GB/T 26572 standard.							X: 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572标准规定的限量要求。 Indicates that the concentration of the hazardous substance in at least one homogeneous material of the part is above the relevant threshold of the GB/T 26572 standard.							电子电气产品的环保使用期限依据SJ/T 11388标准的规定确定。 The EFUP value of EEP is defined according to SJ/T 11388 standard.						
部件名称 (Component Name) T4162214004-005	有害物质 (Hazardous Substance)																																																
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价 铬 (Cr6)	多溴联 苯 (PBB)	多溴二苯 醚 (PBDE)																																											
连接器系统 (Connector Systems)	X	○	○	○	○	○																																											
本表格依据SJ/T 11364标准的规定编制。This table is compiled according to SJ/T 11364 standard.																																																	
○: 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572标准规定的限量要求以下。 Indicates that the concentration of the hazardous substance in all homogeneous materials of the part is below the relevant threshold of the GB/T 26572 standard.																																																	
X: 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572标准规定的限量要求。 Indicates that the concentration of the hazardous substance in at least one homogeneous material of the part is above the relevant threshold of the GB/T 26572 standard.																																																	
电子电气产品的环保使用期限依据SJ/T 11388标准的规定确定。 The EFUP value of EEP is defined according to SJ/T 11388 standard.																																																	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197)																																																
Halogen Content																																																	
Solder Process Capability	Not applicable for solder process capability																																																
Statement of Compliance	Statement of Compliance pdf																																																
Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab																																																
Disclaimer	This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they																																																

oaded from [Arrow.com](#).

provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

M8/M12 SENSOR CABLE ASSEMBLIES
T4162214004-005
RPC-M12-4MR-5.0SH-M12-4FR-
PVC



In-Stock

Connector Type :
Plug/Receptacle
Number of Positions : **4**
Keying : **A**
Housing Material : **GF Nylon**
Cable Assembly Type : **M12 to M12**

TOP RESULTS ?

M8/M12 SENSOR CABLE ASSEMBLIES
T4162214004-007
RPC-M12-4MR-10.0SH-M12-4FR-
PVC



Non-Stocked

Connector Type :
Plug/Receptacle
Number of Positions : **4**
Keying : **A**
Housing Material : **GF Nylon**
Cable Assembly Type : **M12 to M12**

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)