


8SS

Sub-miniature Slide Switches

RoHS Compliant



Specifications

Contact specs.		Silver contacts	
Rating	Max.	125 VAC 6 A 30 VDC 4 A	
	Min.	5 VAC/DC 10 mA	
Initial contact resistance		10 mΩ max.(2~4 VDC 1 A)	
Initial dielectric strength		1,000 VAC 1 minute	
Initial insulation resistance		1,000 MΩ min. (500 VDC)	
Electrical life		ON – ON	30,000 cycles
		ON – OFF – ON	20,000 cycles
Mechanical life		100,000 cycles	
Operating temperature range		-30~+85°C	
Storage temperature range		-40~+85°C	


Part Numbering

8		SS		1		01		1 - Z	
Series Code									
Code	Type	Fig.	Number of poles	Fig.	Switching function	Fig.	Terminal style		
SS	Slide type	1	1 pole	01	ON - ON	1	Solder		
		2	2 poles	02	ON - OFF - ON	2	PC Straight		


Terminal Styles

Solder (Style : 1)	PC Straight (Style : 2)

Panel Cut-Out Dimensions



PC Hole Layouts




Packaging Specifications

Plastic Bag		50 pcs./pack
-------------	--	--------------

SPDT

Solder




S/D

The terminal numbers are not shown on the switch.

Switching function	Viewed from rating marking side		
Part No.			
8SS1011-Z	ON	-	ON
8SS1021-Z	ON	OFF	ON
Connecting terminals	2-1	-	2-3

DPDT

Solder




S/D

The terminal numbers are not shown on the switch.

Switching function	Viewed from rating marking side		
Part No.			
8SS2011-Z	ON	-	ON
★8SS2021-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	-	2-3 5-6

SPDT

PC Straight




P/C

The terminal numbers are not shown on the switch.

Switching function	Viewed from rating marking side		
Part No.			
8SS1012-Z	ON	-	ON
★8SS1022-Z	ON	OFF	ON
Connecting terminals	2-1	-	2-3

DPDT

PC Straight



P/C

The terminal numbers are not shown on the switch.

Switching function	Viewed from rating marking side		
Part No.			
8SS2012-Z	ON	-	ON
★8SS2022-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	-	2-3 5-6

★ : Made to order products.

■Precaution

1. Soldering Specifications

(1) Manual soldering

Device : Solder iron

- ① 420°C Max. 3 sec. Max.

(2) Auto soldering

- ② 275°C Max. 6 sec. Max.

The above-stated soldering conditions shall apply only to switches with straight terminals. Auto soldering is not possible with right-angle terminals. Switches with right-angle terminals should be soldered manually according to the conditions specified in (1) above.

- (3) When soldering two or more terminals to the common land, use the solder resist to isolate the terminals.

3. Mounting

- Do not bend the terminals before mounting the switch on the PC board.
- After mounting the switch, do not place the device in such a way that the device weight will be applied on to the actuator of the switch.
- For switches with straight terminals, solder the switch on the PC board after fixing the switch on the panel with a nut.

2. Flux Cleaning

- (1) Solvent : Fluorine or Alcohol type.
- (2) 8SS series are not washable. To wash the PC board, clean the soldering surface of the PC board with a brush so that the switch is not exposed to the cleaning solution.
- (3) Cleaning after soldering should be done after the terminal temperature falls to 90°C or below, or after leaving the switch for five minutes or longer at room temperature.

■Packaging Specification

Perforated
Plastic
Bags

25 pcs./pack

