



Part Number : [1200655042](#)

Product Description : Micro-Change (M12) Single-Ended Cordset, 12 Poles, A-Coded, Female (Straight) to Pigtail, 26 AWG, PUR/PVC Cable, 5.0m (16.40') Length

Series Number : 120065

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 80C000H45M050




Documents and Resources

Drawings

[1200655042 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset, 12 Poles, A-Coded, Female (Straight) to Pigtail, 26 AWG, PUR/PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	883906851781

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	6.00mm (.236")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	21.885/g
Orientation	Straight to Pigtail
Poles	12
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 20549
Wire Size (AWG)	26

This document was generated on Dec 30, 2025