

Product data sheet

Specifications



InfraStruxure PDU 40kW 208V/208V Transformerless W/ MBP

PDRPPNX10-M

Overview

Presentation	Designed to increase flexibility and agility of data center power distribution through a design that does not require a raised floor.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Number of cables	1
Provided equipment	Installation guide User manual

Physical

Colour	Black
Height	205.7 cm
Width	61 cm
Depth	91.4 cm
Product weight	230 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Network frequency	60 Hz +/- 3 Hz
-------------------	----------------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...3333 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...3048 m

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	218.4 cm
Package 1 Width	121.9 cm
Package 1 Length	91.4 cm
Package 1 Weight	240 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

 Repack and remanufacture	
Take-back	No

Image of product / Alternate images

Alternative

