

PCB header - IMC 1,5/ 9-G-3,5 P20 THR

1830485

<https://www.phoenixcontact.com/us/products/1830485>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



PCB headers, nominal cross section: 1.5 mm², color: black, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Female connector, number of potentials: 9, number of rows: 1, number of positions: 9, number of connections: 9, product range: IMC 1,5/-G-THR, pitch: 3.5 mm, pin layout: Linear double pinning, solder pin [P]: 2 mm, number of solder pins per potential: 2, plug-in system: COMBICON MC 1,5, Pin connector pattern alignment: Standard, locking: without, mounting: without, type of packaging: packed in cardboard

Your advantages

- Designed for integration into the SMT soldering process
- Inverted header with socket contacts for touch-proof device outputs or PCB/PCB connections

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Commercial Data

Item number	1830485
Packing unit	1 pc
Minimum order quantity	50 pc
Sales Key	A01
Product Key	AABTIB
Catalog Page	Page 16 (NTK-2014)
GTIN	4046356886963
Weight per Piece (including packing)	3.382 g
Weight per Piece (excluding packing)	3.22 g
Customs tariff number	85366930
Country of origin	DE

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Technical Data

Product properties

Type	Inverted
Product line	COMBICON Connectors S
Product type	PCB headers
Number of positions	9
Pitch	3.5 mm
Number of connections	9
Number of rows	1
Mounting flange	without
Number of potentials	9
Pin layout	Linear double pinning

Electrical properties

Nominal current I_N	8 A
Nominal voltage U_N	160 V
Pollution degree	3
Contact resistance	2.1 mΩ
Rated voltage (III/3)	160 V
Rated surge voltage (III/3)	2.5 kV
Rated voltage (III/2)	160 V
Rated surge voltage (III/2)	2.5 kV

Mounting

Mounting type THR soldering	THR soldering
Mounting type	THR soldering

Processing notes

Process	Reflow/wave soldering
Moisture Sensitive Level	MSL 1
Classification temperature T_c	260 °C
Solder cycles in the reflow	3

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	hot-dip tin-plated
Metal surface contact area (top layer)	Tin (2 - 4 μm Sn)
Metal surface soldering area (top layer)	Tin (2 - 4 μm Sn)

Material data - housing

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Housing color	black (9005)
Insulating material	LCP
Insulating material group	IIIa
CTI according to IEC 60112	175
Flammability rating according to UL 94	V0

Dimensions

Dimensional drawing	
Pitch	3.5 mm
Width [w]	32.3 mm
Height [h]	8.3 mm
Length [l]	14.5 mm
Installed height	6.3 mm
Solder pin length [P]	2 mm

PCB design

Pin spacing	2.54 mm
-------------	---------

Mechanical tests

Test for conductor damage and slackening

Specification	IEC 60999-1:1999-11
Result	Test passed

Repeated connection and disconnection

Specification	IEC 60999-1:1999-11
Result	Test passed

Pull-out test

Specification	IEC 60999-1:1999-11
Conductor cross section/conductor type/tractive force setpoint/actual value	0.2 mm ² / solid / > 10 N
	0.2 mm ² / flexible / > 10 N
	1.5 mm ² / solid / > 40 N
	1.5 mm ² / flexible / > 40 N

Insertion and withdrawal forces

Result	Test passed
No. of cycles	25
Insertion strength per pos. approx.	3 N
Withdraw strength per pos. approx.	3 N

Contact holder in insert

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Specification	IEC 60512-15-1:2008-05
Contact holder in insert Requirements >20 N	Test passed

Resistance of inscriptions

Specification	IEC 60068-2-70:1995-12
Result	Test passed

Polarization and coding

Specification	IEC 60512-13-5:2006-02
Result	Test passed

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
Result	Test passed

Electrical tests

Thermal test | Test group C

Specification	IEC 60512-5-1:2002-02
Tested number of positions	12

Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	> 5 MΩ

Temperature cycles

Specification	IEC 60999-1:1999-11
Result	Test passed

Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Insulating material group	IIIa
Comparative tracking index (IEC 60112)	CTI 175
Rated insulation voltage (III/3)	160 V
Rated surge voltage (III/3)	2.5 kV
minimum clearance value - non-homogenous field (III/3)	1.5 mm
minimum creepage distance (III/3)	2.5 mm
Rated insulation voltage (III/2)	160 V
Rated surge voltage (III/2)	2.5 kV
minimum clearance value - non-homogenous field (III/2)	1.5 mm
minimum creepage distance (III/2)	1.6 mm
Rated insulation voltage (II/2)	320 V
Rated surge voltage (II/2)	2.5 kV

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

minimum clearance value - non-homogenous field (II/2)	1.5 mm
minimum creepage distance (II/2)	3.2 mm

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 - 60.1 Hz)
Sweep speed	5g (60.1 - 150 Hz)
Test duration per axis	2.5 h

Durability test

Specification	IEC 60512-9-1:2010-03
Impulse withstand voltage at sea level	2.95 kV
Contact resistance R ₁	2.1 mΩ
Contact resistance R ₂	2.3 mΩ
Insertion/withdrawal cycles	25
Insulation resistance, neighboring positions	> 5 MΩ

Climatic test

Specification	ISO 6988:1985-02
Corrosive stress	0.2 dm ³ SO ₂ on 300 dm ³ /40 °C/1 cycle
Thermal stress	100 °C/168 h
Power-frequency withstand voltage	1.39 kV

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------


PCB header - IMC 1,5/ 9-G-3,5 P20 THR

1830485


<https://www.phoenixcontact.com/us/products/1830485>



Drawings



Type: IFMC 1,5/...-ST-3,5 with IMC 1,5/...-G-3,5 P20 THR




PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Dimensional drawing



PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Approvals

	IECEE CB Scheme			
	Approval ID: DE1-60987-B1B2			
		Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG
		160 V	8 A	-
				Cross Section mm ²
				-

	EAC
Approval ID: B.01687	

	cULus Recognized			
	Approval ID: E60425-20110128			
		Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG
Use group B				Cross Section mm ²
		300 V	8 A	-
Use group D				
		300 V	8 A	-
				-

	VDE report with production monitoring			
	Approval ID: 40011723			
		Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG
		160 V	8 A	-
				Cross Section mm ²
				-

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Classifications

ECLASS

ECLASS-9.0	27440402
ECLASS-10.0.1	27440402
ECLASS-11.0	27460201

ETIM

ETIM 8.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PCB header - IMC 1,5/ 9-G-3,5 P20 THR



1830485

<https://www.phoenixcontact.com/us/products/1830485>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com