
Part Number : 2159580336
Product Description : MX-DaSH High-Speed MGE Female Connector Assembly, 31+1 Circuits, Keying Option K, Gray
Series Number : 215958
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2159580336_sd.pdf

2159580150-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2159580000-AS-000.pdf

2159580000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	215958
Description	MX-DaSH High-Speed MGE Female Connector Assembly, 31+1 Circuits, Keying Option K, Gray
Application	Wire-to-Wire, Automotive
Component Type	Receptacle
Product Name	MX-DaSH
Type	Static
UPC	196823256783

Physical

Circuits (maximum)	32
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	24.800/g
Number of Rows	4
Packaging Type	Partitioned Carton

Downloaded from Arrow.com.

Panel Mount	No
Pitch - Mating Interface	3.50mm, 2.75mm, 2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX-DaSH High-Speed MGE Male Connector Assembly, 31+1 Circuits, Keying Option K, Gray	2159580446

Use with Part(s)

Description	Part Number
Use With	1.20mm and 2.80mm AK Female Terminals, MGE Jack

Downloaded from Arrow.com.