









spec ref *				dr Rainbow Zhan		2015/04/14		projection		MM		size A3		scale 3:2		
tolerance std				eng Vicking Liu		2015/10/11						ecn no ELX-DG-22077-1				
ASME Y14.5				chr Fancy Zhang		2015/10/14										
				appr Pei-Ming Zheng		2015/10/14		product family PwrBlade+				rel level Released				
surface 		linear	0.X	±0.5		title IHP + 24S + IHP				dwg no 10106263-2006002				rev B		
			0.XX	±0.25												
ASME Y14.5				0.XXX		±0.10										
		angular	0°	±2°	www.fci.com		cat. no.			Product - Customer Drw				sheet 1 of 3		



Copyright FCI.

PRODUCT NO.	ROW S		HP	SIGNAL						HP																
		E1	P1	1	2	3	4	5	6	P2	E2															
10106263-2006002LF	D C B A		 HE	SD	SD	SD	SD	SD	SD	SC	SC	SC	SC	SC	SC	SB	SB	SB	SB	SA	SA	SA	SA	SA	SA	



CODE	DESCRIPTION
HE	STD HIGH POWER CONTACT (3.05)
SA	STD SIGNAL CONTACT, ROW A (3.05)
SB	STD SIGNAL CONTACT, ROW B (3.05)
SC	STD SIGNAL CONTACT, ROW C (3.05)
SD	STD SIGNAL CONTACT, ROW D (3.05)

dr	Rainbow Zhan	2015/04/14	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2			
eng	Vicking Liu	2015/10/11			ecn no	ELX-DG-22077-1					
chr	Fancy Zhang	2015/10/14			rel level	Released					
appr	Pei-Ming Zheng	2015/10/14			product family	PwrBlade+					
<div></div>			title			IHP + 24S + IHP		dwg no	10106263-2006002	rev	B
RA PF HEADER			cat. no.			Product - Customer Drw			sheet 2 of 3		
www.fci.com											

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.  
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:  
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.  
-SIGNAL CONTACT - COPPER ALLOY.  
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION : 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7)  $1.15\pm0.025$ MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn  
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A  $1.02\pm0.07$ MM HOLE.
- 8) PRODUCT SPECIFICATION : GS-12-658.  
APPLICATION SPECIFICATION : GS-20-141.  
PACKAGE SPECIFICATION: GS-14-1502( PRODUCT PACKAGED IN TRAYS).



Copyright FCI.

dr	Rainbow Zhan	2015/04/14	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2				
eng	Vicking Liu	2015/10/11			ecn no	ELX-DG-22077-1						
chr	Fancy Zhang	2015/10/14				rel level	Released					
appr	Pei-Ming Zheng	2015/10/14	product family		PwrBlade+							
<div></div> <div>www.fci.com</div>			title			IHP + 24S + IHP		dwg no	10106263-2006002	rev	B	
			RA PF HEADER									
cat. no.			Product - Customer Drw					sheet 3 of 3				