


PRODUCT NUMBER

PITCH

TSxx01xB00J0G

7.62 mm





Dim A=(N-1)×7.62+5.6
 Dim B=(N-1)×7.62
 Dim C=(N-1)×7.62
 N=Number of poles

POLES	Tolerance
2p-6p	±0.20
7p-11p	±0.30
12p-16p	±0.40

PART NO.: TS xx 01 x B 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	0 Black (RAL9005)	
03	3 poles	2 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
16	16 poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	



Material

- Item①Top body:Thermoplastic (UL94V-0)
- Item②Bottom body:Thermoplastic (UL94V-0)
- Item③Terminal screw:Steel Zinc plating "-" slot type
- Item④Clamp:Brass, Ni plated
- Item⑤Female contact:PhBz (CuSn) Tin plated

Electrical cULus/TUV

- Voltage rating: 300VAC/750VAC
- Current rating: 15A/15A
- Wire range:0.2-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5 Lb-In 0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus TUV

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK
					angles	MM	title
					radius		TERMINAL BLOCK
					X°±1°	scale	PLUGGABLE PLUG,HOOK ON BACK SIDE,WITHOUT FLANGE
					dr		dwg no
					enrg		sheet 1 of 1
					chr		size
					appd		A4
sheet index	revision	sheet	A	1			type
							CUSTOMER Drawing