


**Q 4 SAK2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 24 A, Number of poles: 4, Pitch in mm (P): 6.00, Insulated: No, Width: 23.4 mm
Order No.	<a href="#">0337200000</a>
Type	Q 4 SAK2.5
GTIN (EAN)	4008190142902
Qty.	50 items

## Q 4 SAK2.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	20.5 mm	Depth (inches)	0.8071 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	23.4 mm	Width (inches)	0.9213 inch
Net weight	6.98 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	CuSn	Colour	grey
----------------	------	--------	------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

## Dimensions

Pitch in mm (P)	6.00 mm
-----------------	---------

## General

Number of poles	4	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Rated voltage	400 V	Nominal current	24 A
---------------	-------	-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		