THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION AUG ,2004.
© COPYRIGHT 2004 By Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.


LOC	DIST
J	—


REVISIONS 変更


P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED ECR-11-015358	12JUL2011	M.T	T.K


−1 & −3 ; AS SHOWN


SHUTTER OPENING DIMENSION











⚠1 MATERIAL
HOUSING, TINE PLATE: THERMOPLASTIC, UL94V−0, BLACK
SIGNAL CONTACT: COPPER ALLOY
POWER CONTACT: COPPER ALLOY
GROUND PLATE : COPPER ALLOY
SHUTTER COVER, SPRING: STAINLESS STEEL
⚠2 FINISH
SIGNAL CONTACT & POWER CONTACT:
Au PL. ON CONTACT AREA
TIN PL. ON SOLDER AREA
Ni UNDER PL. ALL OVER
GROUND PLATE:
6674154−1 TIN PL.(MATTE) / Ni UNDER PL.
6674154−3 SELECTIVE TIN PL. (REFLOW) / Ni UNDER PL.
SHUTTER COVER: BLACK Ni PL.
3 APPLICABLE THICKNESS OF P.C.BOARD: 1.2±0.1mm
4 CONNECTOR TO BE MATED: 6674147−1
5 TRAY MATERIAL; PS COLOR; NATURAL
6 THE DIRECTION OF EACH CONNECTOR ON A TRAY IS REFERRED TO THIS DRAWING.
7 GENERAL TOLERANCE: ±0.3 ±3°
8 QUANTITY: 50EA/TRAY

⚠1 材質
ハウジング: 熱可塑性樹脂 UL94V−0, 黒
シグナルコンタクト: 銅合金
パワーコンタクト: 銅合金
グランドプレート: 銅合金
シャッターカバー、スプリング: ステンレス鋼
⚠2 仕上げ
シグナルコンタクト & パワーコンタクト:
ニッケル下地接点部金めっき、はんだ付け部すずめっき
グランドプレート:
6674154−1 無光沢すずめっき／ ニッケル下地めっき
6674154−3 部分すずめっき (リフロー) / ニッケル下地めっき
シャッターカバー: 黒色ニッケルめっき
3 適用基板厚: 1.2±0.1mm
4 かん合相手型番: 6674147−1
5 トレイ 材質; PS 色; NATURAL
6 トレイの寸法とコネクタの方向は本図を参照のこと
7 一般公差: ±0.3 ±3°
8 数量: 50EA/TRAY

PARTS NUMBER	GROUND PLATE FINISH	SHUTTER COLOR
6674154−3	SELECTIVE TIN−PLATED (REFLOW)	BLACK
6674154−1	TIN−PLATED (MATTE)	BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC ± −
1 PLC ± −
2 PLC ± −
3 PLC ± −
4 PLC ± −
ANGLES ± −
MATERIAL 材料 ⚠1
FINISH 仕上 ⚠2

DWN	30AUG2004 N.SASAME
CHK	30AUG2004 S.KAJINUMA
APVD	09OCT2004 Y.YAMAMOTO
PRODUCT SPEC 製品規格	108−78253
APPLICATION SPEC 取付適用規格	
WEIGHT	3.0g
CUSTOMER DRAWING	

TE Connectivity

NAME 名称: 0.6 DOCKING CONNECTOR W/SHUTTER PLUG 80P + POWER 4P

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A2	00779	C−6674154	—

SCALE 尺度	SHEET	REV
5:1	1 OF 3	D

NOT the LATEST REVISION

6674154

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION AUG , 2004.
© COPYRIGHT 2004 By Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.


LOC	DIST
J	—


REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—


SEMI HARD TRAY ASSY








DETAIL C
SCALE 2:1



Y-Y



6674154

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位： 耗 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差

0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL 材料

FINISH 仕上

DWN

CHK

APVD

PRODUCT SPEC 製品規格

APPLICATION SPEC 取付適用規格

WEIGHT

TE Connectivity

NAME 名称: 0.6 DOCKING CONNECTOR W/SHUTTER PLUG 80P + POWER 4P

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A2	00779	C-6674154	—

CUSTOMER DRAWING

SCALE 尺度 1:1 SHEET 2 OF 3 REV D


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION AUG ,2004.
© COPYRIGHT 2004 By Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

LOC	DIST
J	—

REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位： 耗 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL 材料

FINISH 仕上

DWN

CHK

APVD

PRODUCT SPEC 製品規格

APPLICATION SPEC 取付適用規格

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME 名称: 0.6 DOCKING CONNECTOR W/SHUTTER PLUG 80P + POWER 4P

SIZE	CAGE CODE	DRAWING NO 登号	RESTRICTED TO
A2	00779	C-6674154	—

SCALE 尺度 5:1 SHEET 3 OF 3 REV D

6674154

1471-9 (3/11)

Downloaded from Arrow.com.