TE Connectivity: Every Connection Counts
© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

HARNESSING

HEAT SHRINK BOOTS



✔ Active

TE CONNECTIVITY (TE)

202D174-25/86-0

Raychem

202D174-25/86-0
TE Internal Number: 466824-000
Alias ID: 1193499-7

EU RoHS Compliant
EU ELV Compliant

Lipped Yes

Operating Temperature Range (°C) -55 – 200

Adhesive Options None

Material Systems Code 25

Adhesive Pre-Coat Yes

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Boot, Straight, With Lips
PDF
English

Product Specifications

Product Specification

Thermofit Elastomeric Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable
PDF
English

-25 MOULDED PARTS
PDF
English

Downloaded from Arrow.com.

Product Environmental Compliance

Safety Data Sheet

Aliphatic Polyamide Based Adhesives.

PDF

Dutch

Aliphatic Polyamide Based Adhesives.

PDF

English

Aliphatic Polyamide Based Adhesives.

PDF

French

Aliphatic Polyamide Based Adhesives.

PDF

German

Aliphatic Polyamide Based Adhesives.

PDF

Italian

Aliphatic Polyamide Based Adhesives.

PDF

Spanish

Aliphatic Polyamide Based Adhesives.

PDF

Swedish

Aliphatic Polyamide Based Adhesives.

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

Downloaded from Arrow.com.

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped Yes

Body Features

Material Systems Code 25
Adhesive Pre-Coat Yes
Material Modified Elastomer

Dimensions

Inside Diameter as Supplied 51.8 mm [2.04 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 200

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No
Approved Standards VG95343 Parts 6,7,8 and 9

Other

Adhesive Options None
Adhesive Type High Performance Pre-Coat Adhesive

Statement of Compliance

Downloaded from Arrow.com.

Statement of Compliance

PDF

Downloaded from Arrow.com.