

TM-I
TM-I 23 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

General ordering data

Type	TM-I 23 MC NE WS
Order No.	1428480000
Version	TM-I, Insert markers, 23 x 4 mm, white
GTIN (EAN)	4050118232851
Qty.	400 pc(s).
compatible printer	1324380000

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

TM-I
TM-I 23 MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	4 mm	Width (inches)	0.157 inch
Height	23 mm	Height (inches)	0.906 inch
Depth	2 mm	Depth (inches)	0.079 inch
Net weight	0.225 g		

General data

Colour code	white	Material	Polyamide 66
Material colour according to resistance code	9	Operating temperature range	-40...100 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	V-2	Width	4 mm

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Software	M-Print PRO configuration file

Data sheet

TM-I
TM-I 23 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings