

## Metal Film Resistors, Hermetically-Sealed, Precision, Industrial



### FEATURES

- Hermetic glass enclosure is impervious to harmful environments
- Inert gas filled
- Low noise (- 40 dB)
- Low TCR (down to 15 ppm/°C)

### MECHANICAL SPECIFICATIONS

**Termination:** Vishay Angstrom GSR resistors use gold-plated nickel leads, which are both solderable and weldable (hot solder dip is available as an option).

STANDARD ELECTRICAL SPECIFICATIONS						
MODEL	POWER RATING		MAXIMUM WORKING VOLTAGE <sup>(1)</sup> V	TEMPERATURE COEFFICIENT ± ppm/°C	TOLERANCE ± %	RESISTANCE RANGE Ω
	P <sub>70 °C</sub> W	P <sub>125 °C</sub> W				
GSR55	0.125	0.10	200	15, 25, 50	0.05, 0.1, 0.5, 1	10 to 2.5M
GSR57	0.25	0.125	250	15, 25, 50	0.05, 0.1, 0.5, 1	10 to 1M
GSR60	0.25	0.125	250	15, 25, 50	0.05, 0.1, 0.5, 1	10 to 3M
GSR65	0.50	0.25	300	15, 25, 50	0.05, 0.1, 0.5, 1	10 to 10M
GSR70	0.75	0.50	350	15, 25, 50	0.05, 0.1, 0.5, 1	10 to 10M
GSR75	2.0	1.0	750	15, 25, 50	0.05, 0.1, 0.5, 1	10 to 5M


**Note**

<sup>(1)</sup> Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less.

GLOBAL PART NUMBER INFORMATION																	
New Global Part Numbering: <b>GSR55E49R900BMR</b> (preferred part number format)																	
G	S	R	5	5	E	4	9	R	9	0	0	B	M	R			
GLOBAL MODEL <small>(see Standard Electrical Specifications table)</small>	TEMPERATURE COEFFICIENT <b>X</b> = 15 ppm <b>E</b> = 25 ppm <b>H</b> = 50 ppm		RESISTANCE VALUE <b>R</b> = Ω <b>K</b> = kΩ <b>M</b> = MΩ <b>10R000</b> = 10 Ω <b>49R900</b> = 49.9 Ω <b>680K00</b> = 680 kΩ <b>1M0000</b> = 1.0 MΩ			TOLERANCE CODE <b>A</b> = ± 0.05 % <b>B</b> = ± 0.1 % <b>D</b> = ± 0.5 % <b>F</b> = ± 1.0 %		PACKAGING <b>MR</b> = Foil bag (55, 57, 60) <b>MS</b> = Foil bag (65, 70, 75) <b>CS</b> = Reel (55, 57, 60) <b>CT</b> = Reel (65, 70, 75)			SPECIAL Blank = Standard (Dash Number) (up to 3 digits) From <b>1</b> to <b>999</b> as applicable						
Historical Part Numbering: <b>GSR55E49R9B</b> (will continue to be accepted)																	
GSR55	E		49R9			B											
HISTORICAL MODEL	TEMPERATURE COEFFICIENT		RESISTANCE VALUE			TOLERANCE CODE											

**Note**


- For additional information on packaging, refer to the Through-Hole Resistor Packaging document ([www.vishay.com/doc?31544](http://www.vishay.com/doc?31544)).

**DIMENSIONS** in inches (millimeters)


MODEL	A LENGTH	B DIAMETER	C CL TO CL (MAX.)	D LENGTH $\pm 0.125 (\pm 3.18)$	E DIAMETER $\pm 0.002 (\pm 0.051)$	D APPROX. WEIGHT (G)
GSR55	$0.280 \pm 0.020$ (7.11 $\pm$ 0.51)	$0.110 \pm 0.020$ (2.79 $\pm$ 0.51)	0.379 (9.63)	1.50 (38.10)	0.025 (0.635)	0.337
GSR57	$0.310 \pm 0.025$ (7.87 $\pm$ 0.64)	$0.150 \pm 0.020$ (3.81 $\pm$ 0.51)	0.467 (11.86)	1.50 (38.10)	0.025 (0.635)	0.405
GSR60	$0.425 \pm 0.030$ (10.80 $\pm$ 0.76)	$0.150 \pm 0.020$ (3.81 $\pm$ 0.51)	0.530 (13.46)	1.50 (38.10)	0.025 (0.635)	0.450
GSR65	$0.640 \pm 0.040$ (16.26 $\pm$ 1.02)	$0.240 \pm 0.025$ (6.10 $\pm$ 0.64)	0.780 (19.81)	1.50 (38.10)	0.025 (0.635)	1.300
GSR70	$0.640 \pm 0.040$ (16.26 $\pm$ 1.02)	$0.240 \pm 0.025$ (6.10 $\pm$ 0.64)	0.780 (19.81)	1.50 (38.10)	0.032 (0.813)	1.440
GSR75	$1.062 \pm 0.062$ (26.98 $\pm$ 1.58)	$0.250 \pm 0.025$ (6.35 $\pm$ 0.64)	1.186 (30.12)	1.50 (38.10)	0.032 (0.813)	2.500

**Note**

<sup>(1)</sup> Lead length for product in foil bag pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim.

**POWER DERATING**

**MARKING**

Temperature coefficient: H = 50 ppm, E = 25 ppm, X = 15 ppm  
 Tolerance: F = 1 %, D = 0.5 %, B = 0.1 %, A = 0.05 %

GSR55, GSR57, GSR60, GSR65, GSR70, GSR75: (4 lines)

GSR-55      Style and size  
 24.9  $\Omega$       Value  
 FE          Tolerance and TC  
 1143A      4-digit date code and production lot code



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.