




SCHEMATIC



ELECTRICAL SPECIFICATION @25°C

URNS RATIO

(2-1-3) : (29-30-29)	1CT : 1CT
(5-4-6) : (26-27-25)	1CT : 1CT
(8-7-9) : (23-24-22)	1CT : 1CT
(11-10-12) : (20-21-19)	1CT : 1CT
(14-13-15) : (17-18-16)	1CT : 1CT

CL (16-17)

80uH MIN

POLARITY

2°&29°, 5°&26°
8°&23°, 11°&20°, 14°&17°

INSERTION LOSS

FREQ(MHz)	1	2-300	400	500
dB MAX	0.3	1.0	1.5	2.0

RETURN LOSS

FREQ(MHz)	1-100	200	300	400	500	600
dB MIN	20	18	17	15.5	12.5	10

CM TO DM

REJECTION RATIO

FREQ(MHz)	50	100	200	300	400	500
dB MIN	48	42	36	33	30	28

CM TO CM

REJECTION RATIO

FREQ(MHz)	50	100	200	300	400	500
dB MIN	30	27	24	22	21	20

HIPOT

2250VDC

SUPPORTED BALANCE DC LINE CURRENT TO THE CENTER TAPS
OF TRANSFORMERS ON LINE SIDE :

720mA MAX @57VDC CONTINUOUS

1.2A MAX @57VDC FOR 200 MILLISECONDS



REV. : C

PAGE : 2

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM.	[] METRIC DIM. AS REF.
Alice Pang	2015-01-23	ELECTRICAL SPECIFICATION	S558-10GB-10	TOL. IN INCH	UNIT : INCH [mm]
DRAWN BY	DATE		FILE NAME	.X	SCALE : N/A
ZC Guo	2015-01-23		S55810GB10C.DWG	.XX	SIZE : A4
				.XXX	




THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.




NOTES:

1. STANDARD MARKING REFER TO DOC. HAND-WORK-04.
2. PACKAGE CODE: "QACS001A".
3. PATENT NO : U.S. PAT. 7429195 ; 7924130

SUGGESTED PCB PAD LAYOUT



RoHS



ORIGINATED BY	DATE	TITLE MECHANICAL SPECIFICATION	PART NO. / DRAWING NO.	STANDARD DIM.		[] METRIC DIM. AS REF.		 POWER PROTECT CONNECT
Lawrence Tsang	2016-01-25		S558-10GB-10	TOL. IN INCH		UNIT : INCH [mm]		
DRAWN BY	DATE		FILE NAME	.X		SCALE : N/A		
ZC Guo	2016-01-25			S55810GB10D.DWG	.XX	±0.01		
			.XXX	±0.005				

This document is electronically generated. This is a controlled copy if used internally