




HONEYWELL PART NUMBER
4SX1-H58
PRODUCT CODE VDF0100

REV	DOCUMENT	CHANGED BY	CHECK
10	0038447	SS 28MAR08	BLR

PLASTIC PLUNGER



- NOTE -
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188 ± .002 CENTERS
 - 2 PLATED TERMINALS WILL ACCEPT "AMP INC" .058 DIA PIN RECEPTACLES.
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400° F
 - 4 - SEE SPECIFICATION OF MATING TERMINAL RECEPTACLE FOR TEMPERATURE LIMITATIONS

RELEASE NO.
PR-3391
REPLACES

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ±		DRAWN	SPK	06FEB08	Honeywell			
OPERATING FORCE — — — — 5 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	06FEB08				
RELEASE FORCE — — — — 1 OZ MIN		28 VOLTS DC RATING			0.030 0.015 0.005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL — — — .005 MAX			SEA LEVEL	50,000 FT									
OVERTRAVEL — — — — — .004 MIN		MAXIMUM INRUSH 24 AMP				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		INDUCTIVE	4 AMP	2.5 AMP					B	I	4SX1-H58		10
		RESISTIVE	7 AMP	7 AMP	THIRD ANGLE PROJECTION 								
		APPROVALS						RASTER		SCALE	-	WEIGHT: .003 LB MAX	SHEET
		KEMA, CE	7A 250V ~ T125 5E4 										
		UL, CSA	7A 250 VAC  BRAND L7										