

MOSFET - Power, N-Channel, SUPERFET® III, Automotive, Easy-drive
650 V, 72 mΩ, 44 A
NVHL072N65S3

BV_{DSS}	$R_{DS(on)}$ MAX	I_D MAX
650 V	72 mΩ @ 10 V	44 A



N-Channel MOSFET



TO−247−3LD
CASE 340CX

Description

SuperFET III MOSFET is **onsemi**'s brand−new high voltage super−junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on−resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss provide superior switching performance, and with−stand extreme dv/dt rate. Consequently, SuperFET III MOSFET Easy−drive series helps manage EMI issues and allows for easier design implementation.


Features

- AEC−Q101 Qualified
- Max Junction Temperature 150°C
- Typ. R_{DS}(on) = 61 mΩ
- Ultra Low Gate Charge (Typ. Q_G = 82 nC)
- Low Effective Output Capacitance (Typ. C_{OSS}(eff.) = 724 pF)
- 100% Avalanche Tested
- These Devices are Pb−Free and are RoHS Compliant

Typical Applications

- Automotive PHEV−BEV DC−DC Converter
- Automotive Onboard Charger for PHEV−BEV

MARKING DIAGRAM



$Y	= **onsemi** Logo
&Z	= Assembly Plant Code
&3	= Numeric Date Code
&K	= Lot Code
NVHL072N65S3	= Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, Unless otherwise specified)

Symbol	Parameter		Value	Unit
V_{DSS}	Drain to Source Voltage		650	V
V_{GSS}	Gate to Source Voltage	DC	±30	V
		AC (f > 1 Hz)	±30	V
I_D	Drain Current	Continuous (T_C = 25°C)	44	A
		Continuous (T_C = 100°C)	28	A
I_{DM}	Pulsed Drain Current	Pulsed (Note 1)	110	A
E_{AS}	Single Pulsed Avalanche Energy (Note 2)		214	mJ
E_{AR}	Repetitive Avalanche (Note 1)		3.12	mJ
dv/dt	MOSFET dv/dt		100	V/ns
	Peak Diode Recovery dv/dt (Note 3)		20	V/ns
P_D	Power Dissipation	(T_C = 25°C)	312	W
		Derate Above 25°C	2.5	W/°C
T_J,T_{STG}	Operating and Storage Temperature Range		−55 to +150	°C
T_L	Maximum Lead Temperature for Soldering, 1/8″ from Case for 5 Seconds		300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating: pulse−width limited by maximum junction temperature.
2. I_{AS} = 4.8 A, R_G = 25 Ω, starting T_J = 25°C.
3. I_{SD} < 44 A, di/dt ≤ 200 A/ms, VDD ≤ BVDSS, starting T_J = 25°C.
4. Essentially independent of operating temperature typical characteristics.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta J\,C}$	Thermal Resistance, Junction to Case, Max	0.37	°C/W
$R_{\theta J\,A}$	Thermal Resistance, Junction to Ambient, Max	40	°C/W

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Packing Method	Shipping (Qty / Packing)
NVHL072N65S3	NVHL072N65S3	TO−247−3LD	Tube	30 Units / Tube

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
BV_{DSS}	Drain−to−Source Breakdown Voltage	V_{GS} = 0 V, I_D = 1 mA, T_J = 25°C	650	–	–	V
		V_{GS} = 0 V, I_D = 1 mA, T_J = 150°C	700	–	–	V
ΔBVDSS / ΔTJ	Breakdown Voltage Temperature Coefficient	I_D = 1 mA, Referenced to 25°C	–	0.60	–	V/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = 650 V, V_{GS} = 0 V	–	0.30	1	μA
		V_{DS} = 520 V, V_{GS} = 0 V, Tc = 125°C	–	7.30	–	
I_{GSS}	Gate to Body Leakage Current	V_{GS} = ±30 V, V_{DS} = 0 V	–	–	±100	nA
ON CHARACTERISTICS						
$V_{GS(th)}$	Gate to Source Threshold Voltage	V_{GS} = V_{DS}, I_D = 1.0 mA	2.5	–	4.5	V
$R_{DS(on)}$	Static Drain to Source On Resistance	V_{GS} = 10 V, I_D = 22 A, T_J = 25°C	–	61	72	mΩ
		V_{GS} = 10 V, I_D = 22 A, T_J = 100°C	–	107	–	mΩ
g_{FS}	Forward Transconductance	V_{DS} = 20 V, I_D = 44 A	–	29.7	–	S
DYNAMIC CHARACTERISTICS						
C_{iss}	Input Capacitance	V_{DS} = 400 V, V_{GS} = 0 V, f = 1 MHz	–	3300	–	pF
C_{oss}	Output Capacitance		–	72.8	–	pF
C_{rss}	Reverse Transfer Capacitance		–	14.6	–	pF
$C_{oss(eff.)}$	Effective Output Capacitance	V_{DS} = 0 V to 400 V, V_{GS} = 0 V	–	724	–	pF
$C_{oss(er.)}$	Energy Related Output Capacitance	V_{DS} = 0 V to 400 V, V_{GS} = 0 V	–	104	–	pF
$Q_{g(tot)}$	Total Gate Charge	V_{DS} = 400 V, V_{GS} = 10 V, I_D = 44 A (Note 4)	–	82.0	–	nC
Q_{gs}	Gate to Source Gate Charge		–	23.3	–	nC
Q_{gd}	Gate to Drain “Miller” Charge		–	34.0	–	nC
R_G	Gate Resistance	f = 1 MHz	–	0.685	–	mΩ
SWITCHING CHARACTERISTICS						
$t_{d(on)}$	Turn−On Delay Time	V_{DD} = 400 V, I_D = 44 A, V_{GS} = 10 V, R_G = 4.7 Ω (Note 4)	–	26.3	–	ns
t_r	Turn−On Rise Time		–	50	–	ns
$t_{d(off)}$	Turn−Off Delay Time		–	65.9	–	ns
t_f	Fall Time		–	32	–	ns
DRAIN−SOURCE DIODE CHARACTERISTICS						
I_S	Maximum Continuous Drain to Source Diode Forward Current		–	–	44	A
I_{SM}	Maximum Plused Drain to Source Diode Forward Current		–	–	110	A
V_{SD}	Drain to Source Diode Forward Voltage	V_{GS} = 0 V, I_{SD} = 22 A	–	–	1.2	V
t_{rr}	Reverse Recovery Time	V_{GS} = 0 V, I_{SD} = 44 A dI_F/dt = 100 A/μs	–	576	–	nS
Q_{rr}	Reverse Recovery Charge		–	14.3	–	μC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. Saturation Characteristics




Figure 2. Saturation Characteristics




Figure 3. Transfer Characteristic




Figure 4. On−Resistance Variation vs. Drain Current and Gate Voltage




Figure 5. Forward Diode Characteristics




Figure 6. Capacitance vs. Drain to Source Volatage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (continued)




Figure 7. Gate Charge vs. Gate to Source Voltage




Figure 8. Normalized Drain to Source Breakdown Voltage vs. Junction Temperature




Figure 9. Normalized R_{DSON} vs. Junction Temperature




Figure 10. Forward Bias Safe Operating Area




Figure 11. Maximum Continuous Drain Current vs. Case Temperature




Figure 12. E_{OSS} vs. Drain to Source Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (continued)




Figure 13. Normalized Power Dissipation vs. Case Temperature




Figure 14. Peak Current Capability




Figure 15. E_{OSS} vs. Drain to Source Voltage




Figure 16. Normalized Gate Threshold Voltage vs. Temperature





Figure 17. Normalized Maximum Transient Thermal Impedance


SUPERFET is registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

Downloaded from Arrow.com.

TO−247−3LD
CASE 340CX
ISSUE A

DATE 06 JUL 2020





NOTES: UNLESS OTHERWISE SPECIFIED.

A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
B. ALL DIMENSIONS ARE IN MILLIMETERS.
C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.58	4.70	4.82
A1	2.20	2.40	2.60
A2	1.40	1.50	1.60
D	20.32	20.57	20.82
E	15.37	15.62	15.87
E2	4.96	5.08	5.20
e	~	5.56	~
L	19.75	20.00	20.25
L1	3.69	3.81	3.93
ØP	3.51	3.58	3.65
Q	5.34	5.46	5.58
S	5.34	5.46	5.58
b	1.17	1.26	1.35
b2	1.53	1.65	1.77
b4	2.42	2.54	2.66
c	0.51	0.61	0.71
D1	13.08	~	~
D2	0.51	0.93	1.35
E1	12.81	~	~
ØP1	6.60	6.80	7.00

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON93302G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−247−3LD**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.