

## 473PPA202K

SNUBBER

Parts are RoHS compliant

ic

**APPLICATIONS:** Snubber, IGBT & Power semiconductor power circuits, energy conversion

### ELECTRICAL SPECIFICATIONS

**Capacitance:** 0.047  $\mu$ F

**Dissipation Factor:** 0.0006 Max at 1000 Hz and 25°C

**Temperature Coefficient:** -200 PPM/°C: -100 PPM/°C, 100 PPM/°C

**Ripple Current:** 4.5 A at 100 kHz and 70°C

**ESR:** 16.8 milliOhms (typical) at 100 kHz and 25°C

**Self Inductance:** 1 Nanohenries maximum per mm of body length and lead length

**dvdt:** 2000 V/ $\mu$ s

**Tolerance:** -10 % , +10 %

**Temperature Range:** -40°C to +85°C

Above 85°C the rated (DC/AC) voltage must be derated at per N/A°C

**WVDC:** 2000 Volts DC

**SVDC:** 2600 Volts DC

**VAC:** 650 Volts AC

**Terminal to Terminal Dielectric strength:** 1.6 times the rated DC voltage when applied between the terminals for 10 seconds

**Terminal to case Dielectric strength:** 3000 VAC when applied between the terminals and case for 60 seconds

**Insulation Resistance (Terminal to Terminal):** 30000 MINIMUM after 100 Volts DC is applied for 60 seconds at 20°C

**Reliability:** 300 failures/billion component hours

**Load Life:** 100000/30000 hours at 70°C with 100% of rated voltage

**Capacitance Change:**  $\leq$ 3% of initially measured value

**D.F. Change:**  $\leq$ 200% of maximum specified value

**I.R. Change:**  $>$ 50% of minimum specified value

**Insulation resistance (Terminal to Case):** N/A Megohms MINIMUM after 0 Volts DC is applied for 0 seconds at 0

### PHYSICAL DIMENSIONS

**Diameter (D):** 13 mm, MAX mm


**Length (L):** 34 mm, MAX mm

**Lead Finish:** Matte Tin

**Lead Spacing (S):** mm, +/- mm

**Lead Diameter (d):** 0.8 mm, +/-0.05 mm

**Lead Length (LL):** 35mm, +/- MIN mm



2400 East Devon Avenue Suite 292 Des Plaines, IL 60018 (847) 675-1760 FAX (847) 673-2850

Illinois Capacitor (HK) Ltd., Tel: 85227930931, Fax: 85227930731, [www.illcap.com.hk](http://www.illcap.com.hk)

© Copyright 2020 Illinois Capacitor. An affiliate of Cornell Dubilier, All Rights Reserved