

Part Number Search

You Searched For: 053740-5001 Go

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.
ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

Sales Support
Product Overview
Stock Check

Our Descriptive Part Number: DM537405001
Our Global Manufacturing Part Number: 053740-5001

CONSULT FACTORY	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
CONSULT FACTORY	RoHS compatible =	Compatible with lead free soldering process

Export Compliance		
	Country of Compliance	United States
	Export Compliance Notes	Commercial Shipments "C" Controlled by the US Department of Commerce.

Product Datasheet	
Where Sold	Asia Pacific, Americas, Europe
Product Group	D-Subminiature
Product Sub-Family	D-Sub Combo
Component Type	Size 8 Contact
Application Type	Commercial
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	0
Number of Size 8 contacts	1
Straight or Right Angle	Straight
Contact Plating	Gold over Nickel
Other Features	50 Ohm Coax
Contact Termination	Solder Solder RG316
Temperature Rating	-55°C to +125°C
Current Capacity	5 A
Contact Resistance	8 milli ohms max.
Dielectric Withstanding Voltage	1000 V AC at Sea Level
Insulator Material	Teflon
Contact Material	Copper Alloy
Shell Material	Copper Alloy
Other Information	Coax VSWR less than 1.3:1 up to 500 MHz, Coax Insertion Loss less than .3 dB

© ITT Corporation. All rights reserved. Legal Disclaimer | Privacy Policy | Terms & Conditions

Downloaded from Arrow.com.