







Material
Item ② Terminal body(metal housing): Brass(CuZn), Tin plated
Item ⑤ Terminal screw: Steel Zinc plating "-" slot type
Item ③ Wire guard: Stainless steel
Item ④ Insulator(housing): Thermoplastic (UL94V-0) BLACK

Electrical UL
Voltage rating: 125V
Current rating: 10A
Wire range:
Solid wire(AWG): 16-26
Stranded wire(AWG): 16-26
Torque(Lb-In): 1.7Lb-In
Screw: M2
Wire strip length: 5-6mm
Withstanding Voltage: 1.25KV
Operating temperature: -40°C to +115°C
② Soldering temperature: 260°C±5°C/5 Sec
Safety Approval:

①	WSW P/N	DIM A
	A-TB350-TFxx	3.8
	A-TB350-TFxxBK-A	3.5

DIMENSION	
L	Nx3.5
B	(N-1)x3.5

UL approved WSW P/N		
③	A-TB350-TFxx	YES
	A-TB350-TFxxBK-A	NO

POLES	Tolerance (DimL&B)
2p-5p	±0.15
6p-10p	±0.20
11p-15p	±0.25
16p-20p	±0.35
21p-24p	±0.40

RoHS compliant
Unit: mm
② **us**
File No.: E349947

Scale	Free						Date	Name
TOLERANCE						Drawn	19.04.2010	Alex
X.	±0.50	③	Delete P/N and add UL information	18.05.2021	Daniel	Approved	18.05.2021	Daniel
X.X	±0.30	②	Update to new drawing and add UL	25.03.2016	Amy			
X.XX	±0.10	①	Update	05.09.2011	Lucas			
DIM	TOL	⑥	Drawn	19.04.2010	Alex			
X.°	±1°							
Angle	TOL	Id.	Modification	Date	Name			

Customer-No.	
ASSMANN WSW-No. ③ A-TB350-TFxx A-TB350-TFxxBK-A	
Drawing-No.	rev03
ASS 4092 CO	Sheet 1/1
Replace	