



12TL1-1

(Home : Products : Switches : MICRO SWITCH™ Toggle Switches : TL)

Distributor Inventory

Input part number for stock availability

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option



Actual product appearance may vary.

TL Series Toggle Switch, 2 pole, 3 position, Solder terminal, Standard Lever, Military Part Number MS27735-21



12TL1-1
highres photo



12TL1-1
lowres photo

Sales & Service

Distributor Inventory

Overview

Specs

Documentation

Rich Media

Description

MICRO SWITCH™ TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Features

- Qualified to MIL-DTL-3950
- Environment-proof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range: -85DF to +160DF
- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Product Search

Product Type: All Product Types

☐ New Products Only

Industry: All Industries

☒ Entire Product Catalog

Search Term: Start Here ...

Search

My Links

- eCOM Login
- Request Access to eCOM
- Rep/AD Portal Login
- Rep/AD Portal Access Request
- Sample Request
- Digital U - HVL Learning Hub Login
- Limitless Microsite
- Supplier Microsite

Literature and Media

- Data Sheets
- Videos
- Literature
- Literature Request
- White Papers
- Application Notes
- Application Demos
- CAD Renderings

Contacts

- Customer Service
- Technical Support
- Global Sales & Service