




Part Number : [2219591063](#)
Product Description : CLIK-Mate-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 300.00mm Length, 6 Circuits, White
Series Number : 221959
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings
[2219591063 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	221959
Description	CLIK-Mate-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 300.00mm Length, 6 Circuits, White
Application	Signal, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	CLIK-Mate-to-Pigtail
Product Name	CLIK-Mate
Type	Discrete Wire Assembly
UPC	196823307812

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	White
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Material - Resin	PBT
Net Weight	8.583/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.00mm Pitch CLIK-Mate Vertical Single Row PCB Receptacles	<u>502443</u>
2.00mm Pitch CLIK-Mate Right-Angle Single Row PCB Receptacles	<u>502494</u>

This document was generated on Mar 02, 2026