

Micro Battery

MS Lithium Rechargeable Battery

[MS421R \(Reflowable\)](#)
[MS621R \(Reflowable\)](#)
[MS414GE](#)
[MS412FE](#)
[MS518SE](#)
[MS614SE](#)
[MS621FE](#)
[MS920SE](#)
[MS621T \(Wide temperature range\)](#)
[MS920T \(Wide temperature range\)](#)

TS Lithium Rechargeable Battery

[TS621E](#)
[TS920E](#)

ML Lithium Rechargeable Battery

[ML414H](#)

Chip type Electric Double Layer Capacitor

[CPH3225A](#)
[CPX3225A752D](#)
[CPM3225A](#)

Silver Oxide Battery

[SEIZAIKEN](#)
[Cross reference chart](#)
[SEIZAIKEN's new usage except watches](#)
[Silver Oxide Battery Expiration Guide](#)
[For Your Safety](#)

Micro battery's new challenge for medical devices

Support

Global Network

[Contact Us](#)

[Sitemap](#)

MS Lithium Rechargeable Battery MS518SE


SPECIFICATIONS

Type	MS518SE
Nominal Voltage(V)	3
Charge Voltage (Standard Charge Voltage)(V)	2.8 to 3.3(3.1)
Nominal Capacity(mAh)	3.4
Internal Impedance(Ω)	90
Standard Discharge Current(mA)	0.010
Maximum Discharge Current (Continuous)(mA)	0.15
Cycle Life (Time)100% D.O.D(Depth of Discharge)	100
Cycle Life (Time)20% D.O.D(Depth of Discharge)	1000
Size Diameter(mm)	5.8
Size Height(mm)	1.8
Weight(g)	0.13



MS518SE FL35E

Terminals




+ Click to enlarge


MS518SE is not reflowable. Please mount them on PCB by hand soldering.

CHARACTERISTICS


Click to enlarge.




Charge Voltage Dependence




Charge / Discharge Characteristics




Discharge Characteristics at Various Discharge Current




Overdischarge Characteristics



Discharge Temperature
Characteristics



High Temperature (60°C) Storage
Characteristics



Floating Characteristics (60°C,
applied voltage 3.1V)

Please contact us for more details.

[Inquiry Form](#)