


## Automotive 800 V, 15 A bridge rectifier diode



### Features



- AEC-Q101 qualified
- PPAP capable
- Ultralow conduction losses
- Ultralow reverse losses
- $V_{RRM}$  guaranteed from -40 to +175 °C
- High overcurrent capability
- High creepage DPAK
- MSL: Level 1
- ECOPACK<sup>2</sup> compliant



### Application

- Bridge function
- On board charger (OBC)
- Reverse battery protection
- EV charging stations
- By-Pass function
- O-ring function

### Description

Product status link	
STBR1508-Y	

The STBR1508-Y is a ultralow  $V_F$  rectifier. The high quality design of this diode has produced a device with consistently reproducible characteristics and intrinsic ruggedness. These characteristics make it ideal for heavy duty applications that demand long term reliability like automotive applications.

Thanks to its ultralow conduction losses, the STBR1508-Y is especially suitable for use as input bridge diode in battery chargers and charging stations. It is also ideal for usage in reverse battery protection circuit.

Product summary	
Symbol	Value
$I_{F(AV)}$	15 A
$V_{RRM}$	800 V
$T_j$	-40 to +175 °C
$V_F$ (typ.)	0.88 V

# 1 Characteristics

**Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)**

Symbol	Parameter		Value	Unit
$V_{RRM}$	Repetitive peak reverse voltage		800	V
$V_{RSM}$	Non-repetitive surge reverse voltage		900	V
$I_{F(RMS)}$	Forward rms current		21	A
$I_{F(AV)}$	Average forward current		15	A
$I_{FSM}$	Surge non repetitive forward current		200	A
$T_{stg}$	Storage temperature range		-65 to +175	°C
$T_j$	Operating junction temperature		-40 to +175	°C

**Table 2. Thermal parameters**

Symbol	Parameter	Typ. value	Unit
$R_{th(j-c)}$	Junction to case	0.56	°C/W

For more information, please refer to the following application note :

- AN5088 : Rectifiers thermal management, handling and mounting recommendations

**Table 3. Static electrical characteristics**

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
		$T_j = 25^\circ\text{C}$	$V_R = 800\text{ V}$				
$I_R^{(1)}$	Reverse leakage current	$T_j = 150^\circ\text{C}$	$I_F = 15\text{ A}$	-	5	50	$\mu\text{A}$
		$T_j = 25^\circ\text{C}$		-	1.00	1.09	
$V_F^{(2)}$	Forward voltage drop	$T_j = 150^\circ\text{C}$	$I_F = 15\text{ A}$	-	0.88	0.97	V
		$T_j = 25^\circ\text{C}$		-			

1. Pulse test:  $t_p = 5\text{ ms}$ ,  $\delta < 2\%$

2. Pulse test:  $t_p = 380\text{ }\mu\text{s}$ ,  $\delta < 2\%$

To evaluate the conduction losses, use the following equation:


$$P = 0.75 \times I_{F(AV)} + 0.0147 \times I_{F(RMS)}^2$$

For more information, please refer to the following application notes related to the power losses:


- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses in a power diode

## 1.1 Characteristics (curves)


**Figure 1. Average forward power dissipation versus average forward current**




**Figure 2. Forward voltage drop versus forward current (typical values)**




**Figure 3. Forward voltage drop versus forward current (maximum values)**




**Figure 4. Relative variation of thermal impedance junction to case versus pulse duration**




**Figure 5. Junction capacitance versus reverse voltage applied (typical values)**




**Figure 6. Relative variation of non-repetitive peak surge forward current versus pulse duration (sinusoidal waveform)**




**Figure 7. Relative variation of non-repetitive peak surge forward current versus initial junction temperature (sinusoidal waveform)**



**Figure 8. Non repetitive surge peak forward current versus number of cycles**



**Figure 9. Thermal resistance junction to ambient versus copper surface under tab (typical values, epoxy printed board FR4, e<sub>Cu</sub> = 70 µm)**




## 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 2.1 DPAK HV 2L package information

- Epoxy meets UL 94,VO
- Cooling method: by conduction (C)

Figure 10. DPAK HV 2L package outline




Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Table 4. DPAK HV 2L package mechanical data

Ref.	Dimensions					
	Millimeters			Inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	2.20	2.29	2.40	0.086	0.090	0.095
A1	0.90		1.10	0.035		0.044
A2	0.03		0.23	0.001		0.010
b	0.64	0.76	0.90	0.025	0.030	0.036
b4	5.10	5.20	5.40	0.201	0.204	0.213
c	0.45		0.60	0.017		0.024
c2	0.48		0.60	0.018		0.024
D	6.00		6.20	0.236		0.245
D1	4.60	4.70	4.80	0.181	0.185	0.189
E	6.40		6.60	0.251		0.260
E1	4.95	5.10	5.25	0.194	0.201	0.207
e	2.16	2.28	2.40	0.085	0.090	0.095
e1	4.40		4.60	0.173		0.182
H	9.35		10.10	0.368		0.398
L	1.00		1.50	0.039		0.060
L1	2.60	2.80	3.00	0.102	0.110	0.119
L2	0.65	0.80	0.95	0.025	0.031	0.038
V2	0°		8°	0°		8°

Figure 11. Footprint (dimensions in mm)



Note: For package and tape orientation, reel and inner box dimensions and tape outline please check TN1173.

## 2.1.1 Creepage distance between anode and cathode

**Table 5. Creepage distance between anode and cathode**

Symbol	Parameter	Value	Unit
CdA-K	Minimum creepage distance between A and K	DPAK HV	3.0 mm

**Note:** DPAK HV creepage distance (anode to cathode) =3.0 mm min. (refer to IEC 60664-1)

### 3 Ordering information

**Table 6. Ordering information**

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STBR1508B2Y-TR	BR15 08B2Y	DPAK HV	0.355 g	2500	Tape and reel

## Revision history

**Table 7. Document revision history**

Date	Revision	Changes
17-May-2022	1	First issue.

**IMPORTANT NOTICE – READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics – All rights reserved