

- ?

[Circuit Board Indicators](#)

?

[Panel Mount Indicators](#)

?

[Solid State Lighting](#)

?

[Traffic Signals](#)

?

[Vehicle Lighting](#)

?

[Rail](#)

?


[Obstruction Lighting](#)

?

[Hazardous Area Lighting](#)

?


[Heliport Lighting](#)



Region:

Product Line:


Circuit Board Indicators



Check stock with our distributors now.


5973326607F

Please note that the stock check**is only applicable** to products *within* **Circuit Board Indicators** and **Panel Mount Indicators**.




Please select a Product Line to search.

Circuit Board Indicators



Part No.:

Text Search:



[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp.  
[View PDF File](#)

[Application Notes](#)  
[FAQs](#)

[Dialight Ltd \(UK\)](#)  
[Dialight Garufo](#)  
[Dialight BLP](#)  
[LumiDrives](#)

Circuit Board Indicators - Surface Mount Indicators	
P/N# <b>5973326607F</b>	0603 Package Single Color
Description	

Reverse Current	10 @ Vr =5V
Forward Current Continuous	20 mA
Forward Current Pulse	100 mA
Derating	from 50Â° @ .25mA/Â°C
Reverse Voltage	5 V
Solder Temp	260Â° for 5 sec
Operating Temp	-20~+80° C
Storage Temp	-30~+85° C
Peak Wave Length	530



Operating Characteristics	
LED Position	
Color	Green
Lamp Type	Single Color
LED Type	InGaN
Intensity Min (mcd)	90
Intensity Typ (mcd)	150.0
Intensity Max (mcd)	280.0
Fwd Voltage Min	3.4
Fwd Voltage Typ	3.8
Fwd Voltage Max	525
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	76
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

