



MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2AW8557-D6




NOTES

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø .139 MAX ON 1.000±.002 CENTERS
- 2 - SUITABLE ONLY FOR APPLICATIONS IMPARTING A RAPID STROKE TO THE SWITCH PLUNGER
- 3 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE
- ④ CHARACTERISTICS TAKEN AT POINT A

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS ④

OPERATING FORCE ——— 8 1/2 OZ MAX
RELEASE FORCE ——— 1 1/2 OZ MIN
DIFFERENTIAL TRAVEL — .008 - .030
OVERTRAVEL ——— .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SEE CIRCUIT DIAGRAM

L73 15A 125, 250 OR 480 VAC
1A 125 VDC, 0.5A 250 VDC
1/4HP 125 VAC, 1/2HP 250 VAC



SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT

CATALOG LISTING
BZ-2AW8557-D6
PAGE 1 OF 1

ISSUE
M

3

REVISIONS

A	203596
CSL	27 JUL 01
B	206178
CSL	7 AUG 02

REPLACES X113237-BZ
203327
RELEASE NO.
CHECK
19 JUN 01
SAV
CHECK
19 JUN 01
C SL
DRAWN
RASTER