



Part Number : 1200652151
Product Description : Micro-Change (M12)
Single-Ended Cordset, 5 Poles, Male (Straight)
to Pigtail, 18 AWG, Yellow TPE Cable, 5.0m
(16.40') Length
Series Number : 120065
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 805006K03M050



Documents & Resources

Drawings
[1200652151_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 18 AWG, Yellow TPE Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	78172509212

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	6.86mm (.270")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail

Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	441.700/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	18

This document was generated on Apr 26, 2025
