

Datasheet

N-channel 600 V, 230 mΩ typ., 13 A, MDmesh M6 Power MOSFET in a TO-220FP package



TO-220FP



Features

Order code	V_{DS}	$R_{DS(on)}$ max.	I_D
STF18N60M6	600 V	280 mΩ	13 A

- Reduced switching losses
- Lower $R_{DS(on)}$ per area vs previous generation
- Low gate input resistance
- 100% avalanche tested
- Zener-protected

Applications

- Switching applications
- LLC converters
- Boost PFC converters

Description

The new MDmesh M6 technology incorporates the most recent advancements to the well-known and consolidated MDmesh family of SJ MOSFETs. STMicroelectronics builds on the previous generation of MDmesh devices through its new M6 technology, which combines excellent $R_{DS(on)}$ per area improvement with one of the most effective switching behaviors available, as well as a user-friendly experience for maximum end-application efficiency.

Product status link
STF18N60M6

Product summary	
Order code	STF18N60M6
Marking	18N60M6
Package	TO-220FP
Packing	Tube

Downloaded from Arrow.com.

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{GS}	Gate-source voltage	±25	V
I_D	Drain current (continuous) at T_{case} = 25 °C	13	A
	Drain current (continuous) at T_{case} = 100 °C	8.2	
I_{DM}(1)	Drain current (pulsed)	38	A
P_{TOT}	Total power dissipation at T_{case} = 25 °C	25	W
dv/dt(2)	Peak diode recovery voltage slope	15	V/ns
dv/dt(3)	MOSFET dv/dt ruggedness	100	
V_{ISO}	Insulation withstand voltage (RMS) from all three leads to external heat sink (t = 1 s; T_{case} = 25 °C)	2.5	kV
T_{stg}	Storage temperature range	-55 to 150	°C
T_j	Operating junction temperature range		

1. *Pulse width is limited by safe operating area.*
2. *I_{SD} ≤ 13 A, di/dt ≤ 400 A/µs, $V_{DS(peak)}$ < $V_{(BR)DSS}$, V_{DD} = 400 V*
3. *V_{DS} ≤ 480 V*

Table 2. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj\text{-}case}$	Thermal resistance junction-case	5	°C/W
$R_{thj\text{-}amb}$	Thermal resistance junction-ambient	62.5	°C/W

Table 3. Avalanche characteristics

Symbol	Parameter	Value	Unit
I_{AR}	Avalanche current, repetitive or non-repetitive (pulse width limited by T_{Jmax})	2.7	A
E_{AS}	Single pulse avalanche energy (starting T_j = 25 °C, I_D = I_{AR}, V_{DD} = 50 V)	210	mJ

Downloaded from Arrow.com.

2 Electrical characteristics

(T_{case} = 25 °C unless otherwise specified).

Table 4. On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	V_{GS} = 0 V, I_D = 1 mA	600			V
I_{DSS}	Zero gate voltage drain current	V_{GS} = 0 V, V_{DS} = 600 V			1	µA
		V_{GS} = 0 V, V_{DS} = 600 V, T_{case} = 125 °C(1)			100	
I_{GSS}	Gate-body leakage current	V_{DS} = 0 V, V_{GS} = ±25 V			±5	µA
$V_{GS(th)}$	Gate threshold voltage	V_{DS} = V_{GS}, I_D = 250 µA	3.25	4	4.75	V
$R_{DS(on)}$	Static drain-source on-resistance	I_D = 6.5 A, V_{GS} = 10 V		230	280	mΩ

1. *Defined by design, not subject to production test.*

Table 5. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}	Input capacitance	V_{DS} = 100 V, f = 1 MHz, V_{GS} = 0 V	-	650	-	pF
C_{oss}	Output capacitance		-	45	-	
C_{rss}	Reverse transfer capacitance		-	2	-	
$C_{oss\ eq.}$(1)	Equivalent output capacitance	V_{DS} = 0 to 480 V, V_{GS} = 0 V	-	123	-	pF
R_G	Intrinsic gate resistance	f = 1 MHz, I_D = 0 A	-	4.6	-	Ω
Q_g	Total gate charge	V_{DD} = 480 V, I_D = 13 A, V_{GS} = 0 to 10 V (see Figure 14. Test circuit for gate charge behavior)	-	16.8	-	nC
Q_{gs}	Gate-source charge		-	4.5	-	
Q_{gd}	Gate-drain charge		-	8.4	-	

1. *$C_{oss\ eq.}$ is defined as a constant equivalent capacitance giving the same charging time as C_{oss} when V_{DS} increases from 0 to 80% V_{DSS}.*

Table 6. Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	V_{DD} = 300 V, I_D = 6.5 A, R_G = 4.7 Ω, V_{GS} = 10 V (see Figure 13. Test circuit for resistive load switching times and Figure 18. Switching time waveform)	-	16	-	ns
t_r	Rise time		-	7	-	
$t_{d(off)}$	Turn-off delay time		-	28	-	
t_f	Fall time		-	9	-	

Downloaded from Arrow.com.

Table 7. Source-drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{SD}	Source-drain current		-		13	A
I_{SDM} (1)	Source-drain current (pulsed)		-		38	A
V_{SD} (2)	Forward on voltage	I_{SD} = 13 A, V_{GS} = 0 V	-		1.6	V
t_{rr}	Reverse recovery time	I_{SD} = 13 A, di/dt = 100 A/µs, V_{DD} = 60 V (see Figure 15. Test circuit for inductive load switching and diode recovery times)	-	208		ns
Q_{rr}	Reverse recovery charge		-	1.9		µC
I_{RRM}	Reverse recovery current		-	18		A
t_{rr}	Reverse recovery time	I_{SD} = 13 A, di/dt = 100 A/µs, V_{DD} = 60 V, T_j = 150 °C (see Figure 15. Test circuit for inductive load switching and diode recovery times)	-	290		ns
Q_{rr}	Reverse recovery charge		-	2.9		µC
I_{RRM}	Reverse recovery current		-	20		A

1. *Pulse width is limited by safe operating area.*
2. *Pulsed: pulse duration = 300 µs, duty cycle 1.5%*

Downloaded from Arrow.com.

2.1 Electrical characteristics (curves)

Figure 1. Safe operating area




Figure 2. Thermal impedance




Figure 3. Output characteristics




Figure 4. Transfer characteristics




Figure 5. Gate charge vs gate-source voltage





Figure 6. Static drain-source on-resistance



Downloaded from Arrow.com.

Figure 7. Capacitance variations




Figure 8. Output capacitance stored energy




Figure 9. Normalized gate threshold voltage vs temperature




Figure 10. Normalized on-resistance vs temperature




Figure 11. Normalized $V_{(BR)DSS}$ vs temperature





Figure 12. Source-drain diode forward characteristics



Downloaded from Arrow.com.

3 Test circuits

Figure 13. Test circuit for resistive load switching times




Figure 14. Test circuit for gate charge behavior




Figure 15. Test circuit for inductive load switching and diode recovery times




Figure 16. Unclamped inductive load test circuit




Figure 17. Unclamped inductive waveform





Figure 18. Switching time waveform



Downloaded from Arrow.com.


4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

Downloaded from Arrow.com.

4.1 TO-220FP package information

Figure 19. **TO-220FP package outline**



Downloaded from Arrow.com.

Table 8. **TO-220FP package mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A	4.4		4.6
B	2.5		2.7
D	2.5		2.75
E	0.45		0.7
F	0.75		1
F1	1.15		1.70
F2	1.15		1.70
G	4.95		5.2
G1	2.4		2.7
H	10		10.4
L2		16	
L3	28.6		30.6
L4	9.8		10.6
L5	2.9		3.6
L6	15.9		16.4
L7	9		9.3
Dia	3		3.2

Downloaded from Arrow.com.

Revision history

Table 9. **Document revision history**

Date	Version	Changes
15-Nov-2018	1	First release.
19-Apr-2019	2	Updated product status link table in cover page.

Downloaded from Arrow.com.

Contents

1 **Electrical ratings** 2

2 **Electrical characteristics** 3

2.1 Electrical characteristics (curves) 5

3 **Test circuits** 7

4 **Package information** 8

4.1 TO-220FP package information 8

Revision history 11

Downloaded from Arrow.com.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved

Downloaded from Arrow.com.