348989-1 ✔ ACTIVE


Econoseal

TE Internal #: 348989-1

Single Wire Seal (SWS), 4.4 mm [.173 in] Cavity Diameter, -40 – 130 °C [-40 – 266 °F], Red, Silicone

View on TE.com >

Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Cavity Diameter: **4.4 mm [.173 in]**

Operating Temperature Range: **-40 – 130 °C [-40 – 266 °F]**

Primary Product Color: **Red**

Primary Product Material: **Silicone**

Features

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)

Body Features

Primary Product Color	Red
Primary Product Material	Silicone

Dimensions

Cavity Diameter	4.4 mm[.173 in]
Compatible Insulation Diameter Range	1.5 – 2.4 mm[.059 – .094 in]

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
Operating Temperature (Max)	130 °C[266 °F]

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	40
Contains Lubricant	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant

Downloaded from Arrow.com.

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Customers Also Bought



TE Part #444430-1
SINGLE WIRE SEAL



TE Part #626065
2 P FASTIN-ON 110 HOUSING TAB PA66 NAT



TE Part #626094-2
FF .250 REC 0.5 /1.0 MM2 0.32X19.3 TPBR




TE Part #880634-5
FF 110 REC 0.5-1.0 MM2 0.25 X 12.3 PTPBR



TE Part #880636-2
FF 250 TAB 1.0-2.5 MM2 0.39 X 13.2 TPBR



TE Part #880688-2
FF 250 TERMINAL 0.5-1.0MM2 0.39 X13.2TPBR



TE Part #881778-1
KIT ECONOSEAL J 6PO




TE Part #964284-2
JPT A REC 2.8 Contact SRC Sn

Downloaded from Arrow.com.



TE Part #1989581-1
SPECIAL MICRO TIMER REC.



TE Part #881593-1
ECONOSEAL TAB .070

Documents

3D PDF

3D

Customer View Model

ENG_CVM_CVM_348989-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_348989-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_348989-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Product Datasheet

English

Downloaded from Arrow.com.