

PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PT protective connector with protective circuit for two 2-wire floating signal circuits. 5 V DC nominal voltage. HART-compatible.

Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

Item number	2838241
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL21
Product key	CL2111
GTIN	4017918182656
Weight per piece (including packing)	26.08 g
Weight per piece (excluding packing)	20.9 g
Customs tariff number	85363010
Country of origin	DE

PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Technical data

Product properties

Product type	Surge protection for MCR technology
Product family	PLUGTRAB PT
IEC test classification	C1
	C2
	C3
	D1
Type	Male
Surge protection fault message	none
Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00
Wire pairs per module	2

Insulation characteristics

Overvoltage category	III
----------------------	-----


Electrical properties

Nominal voltage U_N	5 V DC
-----------------------	--------

Connection data

Connection method	Screw connection (in connection with the base element)
Screw thread	M3
Tightening torque	0.8 Nm
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	17.5 mm
Height	44.8 mm
Depth	51.7 mm
Horizontal pitch	1 Div.
Complete module width	17.7 mm
Complete module height	90 mm
Complete module depth	65.5 mm

Material specifications

PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Color	black (RAL 9005)
	copper color
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground
Maximum continuous operating voltage U_C	6 V DC
	4 V AC
Rated current	450 mA (45 °C)
Operating effective current I_C at U_C	≤ 1 mA
Protective conductor current I_{PE}	≤ 1 μ A (with PT 2X2+F-BE)
	≤ 4 μ A
Nominal discharge current I_n (8/20) μ s (line-line)	10 kA
Nominal discharge current I_n (8/20) μ s (line-ground)	10 kA
Pulse discharge current I_{imp} (10/350) μ s	2.5 kA (per path)
Total discharge current I_{Total} (8/20) μ s	20 kA
Max. discharge current I_{max} (8/20) μ s maximum (line-line)	10 kA
Max. discharge current I_{max} (8/20) μ s maximum (line-earth)	10 kA
Output voltage limitation at 1 kV/ μ s (line-line) spike	≤ 12 V
Output voltage limitation at 1 kV/ μ s (line-earth) spike	≤ 450 V
Output voltage limitation at 1 kV/ μ s (line-line) static	≤ 10 V
Residual voltage at I_n (conductor-conductor)	≤ 10 V
Residual voltage at I_n (line-signal ground)	≤ 450 V
Residual voltage with I_{an} (10/1000) μ s (line-line)	≤ 12 V
Response time t_A (line-line)	≤ 1 ns
Response time t_A (line-earth)	≤ 100 ns
Input attenuation aE, sym.	0.5 dB (≤ 200 kHz)
Cut-off frequency f_g (3 dB), sym. in 50 Ω system	typ. 1 MHz
Capacity (Core-Core)	6 nF
Resistance per path	2.2 Ω
Surge protection fault message	none
Impulse durability (line-line)	C2 - 10 kV / 5 kA
Impulse durability (line-earth)	C2 - 10 kV / 5 kA
	D1 - 2.5 kA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	VDE 0110-1 / IEC 60664-1
-----------------------	--------------------------

Standards Information technology specification

Standards/regulations	IEC 61643-21
	DIN EN 61643-21
	UL 497B
	IEC 61643-21
	DIN EN 61643-21
	UL 497B
Standards/specifications	IEC 61643-21
Note	2000

Mounting

Mounting type	on base element
---------------	-----------------

PT 2X2- 5DC-ST - Surge protection plug

2838241

<https://www.phoenixcontact.com/us/products/2838241>




Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram



PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2838241>

UL Listed Approval ID: FILE E 138168				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	5 V	0.45 A	-	-

cUL Listed Approval ID: FILE E 333250				
--	--	--	--	--

UL Listed Approval ID: FILE E 333250				
---	--	--	--	--

PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Classifications

ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

ETIM

ETIM 9.0	EC000943
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

PT 2X2- 5DC-ST - Surge protection plug



2838241

<https://www.phoenixcontact.com/us/products/2838241>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b6687aed-12d1-4706-ae54-8688884e9564

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com