


SPECIFICATION CONTROL DRAWING			5022D1312
CHEMINAX	50 OHM, AWG 22, 19 STRANDS OF AWG 34, COAXIAL CABLE	Date	3-28-13
		Revision	H
THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.			
CONSTRUCTION DETAILS		ELECTRICAL CHARACTERISTICS	
DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED. 		CHARACTERISTIC IMPEDANCE 50 ± 2 ohms, Method A	
		CAPACITANCE 27.9 pF/ft. (nominal)	
		VELOCITY OF PROPAGATION 73% (nominal)	
		ATTENUATION 13.0 dB/100 ft. (maximum) at 400 MHz	
		ADDITIONAL REQUIREMENTS	
		<u>ELECTRICAL</u>	
		CONDUCTOR RESISTANCE 14.4 ohms/1000 ft. (nominal)	
		INSULATION RESISTANCE 10,000 megohms (minimum) for 1000 ft.	
		JACKET FLAWS	
		SPARK TEST 1.0 kV (rms)	
		IMPULSE TEST 6.0 kV (peak)	
		VOLTAGE WITHSTAND (DIELECTRIC) 1000 volts (rms) (minimum)	
		<u>ENVIRONMENTAL</u>	
		FLAMMABILITY Method C	
		HEAT SHOCK 225°C	
		LOW TEMPERATURE-COLD BEND -55°C/3.50 inch mandrel	
		VOLTAGE WITHSTAND (Post Environmental) 1000 volts (rms), 1 minute	
		<u>PHYSICAL</u>	
		INSULATION (DIELECTRIC)	
		ELONGATION 50% (minimum)	
		TENSILE STRENGTH 1000 lbf/in ² (minimum)	
		JACKET	
		ELONGATION 200% (minimum)	
		TENSILE STRENGTH 2000 lbf/in ² (minimum)	
		JACKET THICKNESS .009 inch (minimum)	
		.015 inch (maximum)	
		SHIELD COVERAGE 90% (minimum)	
Outer jacket color will be black (designated by a "-0" appended to the part number, e.g. 5022D1312-0) unless otherwise specified.		WEIGHT 11.8 lbs/1000 ft. (nominal)	
Designate outer jacket color with a dash number in accordance with MIL-STD-681. Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.			
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.			
Page 1 of 1	Rayfoam, Thermorad, Cheminax, Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.		



Raychem Wire & Cable
 501 Oakside Avenue
 Redwood City, California 94063-3800
 1-800-227-8816 Fax: 1-650-361-6297

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.