







PCB Layout, Component side  
thickness 1.6 mm



## SPECIFICATION

|                       |          |
|-----------------------|----------|
| Mating Cycles         | 500      |
| Filter type           | C        |
| Capacitance           | 47pf±20% |
| Working Voltage       | 100v     |
| Current Rating        | 7,5A     |
| Insulation Resistance | >1GΩ     |

| FREQUENCY<br>(MHz) | ATTENUATION<br>dB |
|--------------------|-------------------|
| 5                  | -                 |
| 10                 | -                 |
| 50                 | -                 |
| 100                | -                 |
| 500                | 30dB              |
| 1000               | 35dB              |

|             |            |  |       |              |      |                               |              |      |                                                                                       |                                                                                                           |                                  |                          |
|-------------|------------|--|-------|--------------|------|-------------------------------|--------------|------|---------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|----------------------------------|--------------------------|
|             |            |  |       |              |      |                               | Dat.         | Name |  | D-Sub, female, straight,<br>9 Poles, solder pins,<br>tin plated shell with<br>spacer nuts and board-locks | Mo?Ms lab/<br>Scale<br><br>1.5:1 |                          |
|             |            |  |       |              |      | Detail.                       | 8 - JUL - 02 | CV   |                                                                                       |                                                                                                           |                                  |                          |
|             |            |  |       |              |      | Insp.                         |              |      |                                                                                       |                                                                                                           |                                  | All Dim. in mm           |
|             |            |  |       |              |      | Stand.                        |              |      |                                                                                       |                                                                                                           |                                  | Orig. Size DIN A 4       |
| 09641127216 | M3         |  | 33094 | 04/10/05     | JMDR | HARTING EURL<br>F-95972 Paris |              |      |                                                                                       |                      | TB 0964112721x                   | Blatt/ Page<br><br>2 / 3 |
| 09641127215 | UNC 4-40   |  | 31058 | 8 - JUL - 02 | CV   |                               |              |      |                                                                                       |                                                                                                           |                                  |                          |
| Part number | Nut thread |  | Mod.  | Dat.         | Name |                               |              |      |                                                                                       |                                                                                                           |                                  |                          |