


ECASD60J227M010K00



Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
K	330Embossed Tape	2500

Mass (typ.)	
1 piece	0.2g

Attention
 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 2.This datasheet has only typical specifications because there is no space for detailed specifications.
 Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

ECASD60J227M010K00



Specifications

Length	7.3±0.3mm
Width	4.3±0.2mm
Thickness	2.8±0.3mm
Allowable Ripple Current	3.0Arms
Capacitance	220µF ±20%
ESR	10mΩ
Leakage Current	138.6µA
Maximum operating temperature	105°C
Operating Temperature Range	-40°C to 105°C
Rated Voltage	6.3Vdc
Size code in inch (mm)	2917(7343)
S size	1.3±0.2mm
Capacitance change rate	±20%
W1 size	2.4±0.2mm


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


ECASD60J227M010K00

Characteristic Data


The charts below may show another part number which shares its characteristics.




■ ECASD60J227M010K00 |Z| DCOV, 25degC



■ ECASD60J227M010K00 R DCOV, 25degC



■ ECASD60J227M010K00 C-DC bias capchange, 25.0degC, AC1




■ ECASD60J227M010K00 C-AC Voltage capchange, DCOV, 25.0


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

ECASD60J227M010K00



■ ECASD60J227M010K00 C-Temp. capchange, DCOV, AC1Vrms



■ ECASD60J227M010K00 S21 DCOV, 25degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.