



**Part Number :** [191640018](#)

**Product Description :** Perma-Seal Female Quick Disconnect Receptacle for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier

**Series Number :** 19164

**Status :** Active

**Product Category :** Quick Disconnects

**Engineering Part Number :** SAA-9261T



---

## Documents and Resources

### Drawings

[191640018\\_sd.pdf](#)


### Specifications

[PS-19902-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Female Quick Disconnect Receptacle for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier
Product Name	Perma-Seal
Type	Standard Quick Disconnect
UPC	800753113060

### Agency

CSA	LR18689
UL	E79133

### Electrical

Voltage - Maximum	600V
-------------------	------

### Physical

Barrel Type	Closed
Color - Resin	Red
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	NiAc
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.733/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	4.32mm max.
Wire Size (AWG)	18, 20, 22

---

## Application Tooling

### Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u><a href="#">192880095</a></u>

---

This document was generated on May 20, 2026