
Part Number : 1201088539
Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, D-Coded, Male (90°) to Pigtail, 24 AWG, Teal PUR WSOR Cable, 5.0m (16.40') Length
Series Number : 120108
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E10A00716M050



Documents and Resources

Drawings

1201088539_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120108
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, D-Coded, Male (90°) to Pigtail, 24 AWG, Teal PUR WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	889056898836

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Cable Diameter	6.50mm (.256")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy

Downloaded from Arrow.com.

Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	286.500/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-40° to +80°C
Wire/Cable Type	Shielded TPE/AWM 21215
Wire Size (AWG)	24

Downloaded from Arrow.com.