SIEMENS

Data sheet 3RH2911-1HA22



auxiliary switch, on the front, 2 NO + 2 NC, .1/.2, .1/.2, .3/.4, .3/.4, current path: 1 NC, 1 NC, 1 NO, 1 NO, screw terminal, for contactors 3RT2 and contactor relays 3RH2

product brand name	SIRIUS
product category	Auxiliary switch
product designation	auxiliary switch
design of the product	for snapping onto the front
product type designation	3RH29
suitability for use	for 3RT2.1, 3RT2.2, 3RT2.3, 3RT2.4, 3RH2
General technical data	
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
protection class IP on the front	IP20
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	200 000
Substance Prohibitance (Date)	10/01/2009
Net Weight	55 g
number of NC contacts for auxiliary contacts	
● instantaneous contact	2
● lagging switching	0
number of NO contacts for auxiliary contacts	
● instantaneous contact	2
● leading contact	0
number of CO contacts of auxiliary contacts instantaneous contact	0
operational current at AC-15 at 690 V rated value	1 A
operational current of auxiliary contacts at AC-12	
● at 24 V	10 A
● at 230 V	10 A
operational current of auxiliary contacts at AC-14	
● at 125 V	6 A
● at 250 V	6 A
operational current of auxiliary contacts at AC-12 maximum	10 A
operational current of auxiliary contacts at AC-15	
● at 24 V	6 A
● at 230 V	6 A
● at 400 V	3 A
operational current of auxiliary contacts at DC-12	
● at 24 V	10 A
● at 110 V	3 A
● at 220 V	1 A
operational current with 2 current paths in series at DC-12	

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

● at 24 V rated value	10 A
● at 60 V rated value	10 A
● at 110 V rated value	4 A
● at 220 V rated value	2 A
● at 440 V rated value	1.3 A
● at 600 V rated value	0.65 A
operational current with 3 current paths in series at DC-12	
● at 24 V rated value	10 A
● at 60 V rated value	10 A
● at 110 V rated value	10 A
● at 220 V rated value	3.6 A
● at 440 V rated value	2.5 A
● at 600 V rated value	1.8 A
operational current with 2 current paths in series at DC-13	
● at 24 V rated value	10 A
● at 60 V rated value	3.5 A
● at 110 V rated value	1.3 A
● at 220 V rated value	0.9 A
● at 440 V rated value	0.2 A
● at 600 V rated value	0.1 A
operational current with 3 current paths in series at DC-13	
● at 24 V rated value	10 A
● at 60 V rated value	4.7 A
● at 110 V rated value	3 A
● at 220 V rated value	1.2 A
● at 440 V rated value	0.5 A
● at 600 V rated value	0.26 A
operational current of auxiliary contacts at DC-13	
● at 24 V	6 A
● at 48 V	2 A
● at 60 V	2 A
● at 110 V	1 A
● at 125 V	0.9 A
● at 220 V	0.3 A
● at 250 V	0.3 A
design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V	C characteristic: 10 A; 0.4 kA
contact reliability of auxiliary contacts	1 faulty switching per 100 million (17 V, 1 mA)
Ambient conditions	
ambient temperature	
● during operation	-25 ... +60 °C
● during storage	-55 ... +80 °C
Safety related data	
product function	
● mirror contact according to IEC 60947-4-1	Yes; with 3RT2
● positively driven operation according to IEC 60947-5-1	Yes
Short-circuit protection	
design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V	C characteristic: 10 A; 0.4 kA
design of the fuse link for short-circuit protection of the auxiliary switch required	gG: 10 A (690 V, 1 kA)
Installation/ mounting/ dimensions	
fastening method	snap-on mounting
height	37.5 mm
width	36 mm
depth	43.7 mm
Connections/ Terminals	
type of electrical connection for auxiliary and control circuit	screw-type terminals
connectable conductor cross-section for auxiliary contacts	

© Copyright Siemens
Downloaded from Arrow.com.

● solid or stranded	0.5 ... 2.5 mm²
● finely stranded with core end processing	0.5 ... 2.5 mm²
type of connectable conductor cross-sections	
● for auxiliary contacts	
— solid or stranded	2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)
— finely stranded with core end processing	2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)
● for AWG cables for auxiliary contacts	2x (20 ... 16), 2x (18 ... 14)
AWG number as coded connectable conductor cross section for auxiliary contacts	20 ... 14

Approvals Certificates

Environmental Product Declaration

● global warming potential [CO2 eq] / during manufacturing	0.34 kg
● global warming potential [CO2 eq] / during operation	0.562 kg
● global warming potential [CO2 eq] / after end of life	0.0172 kg
● global warming potential [CO2 eq] / total	0.92 kg

Environment | **General Product Approval**

Environmental Confirmations

Functional Saftey | **Maritime application**


Type Examination Certificate

Maritime application


Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RH2911-1HA22
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RH2911-1HA22
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3RH2911-1HA22
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RH2911-1HA22&lang=en

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.




Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.




Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

3RT2



3RH2



last modified: 9/8/2025

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.