

	1	2	3	4	5	6	7																																																																												
A	⑤ USB 2.0 COMPLIANT							A																																																																											
B								B																																																																											
C								C																																																																											
D								D																																																																											
E								E																																																																											
F								F																																																																											
G	RoHS compliant Unit: mm							G																																																																											
H	<table border="1"> <thead> <tr> <th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th>Date</th><th>Name</th><th>Customer-No.</th></tr> </thead> <tbody> <tr> <td>TOLERANCE</td><td></td><td>⑤</td><td>Add "USB 2.0 COMPLIANT"</td><td>19.08.2013</td><td>Amy</td><td>Drawn</td><td>04.05.2007</td><td>Hellwig</td></tr> <tr> <td>X.X</td><td>±0.3</td><td>④</td><td>Update</td><td>08.06.2013</td><td>Winnie</td><td>Approved</td><td>19.08.2013</td><td>Amy</td></tr> <tr> <td>X.XX</td><td>±0.20</td><td>③</td><td>Update</td><td>07.07.2009</td><td>Stefanie</td><td></td><td></td><td></td></tr> <tr> <td>X.XXX</td><td>±0.100</td><td>②</td><td>To adapt</td><td>11.09.2007</td><td>N.Schulz</td><td colspan="3" rowspan="3"> ASSMANN WWS components </td></tr> <tr> <td>DIM</td><td>TOL</td><td>①</td><td>Production plant change</td><td>04.05.2007</td><td>Hellwing</td></tr> <tr> <td>ANG.</td><td>±1°</td><td></td><td></td><td></td><td></td></tr> <tr> <td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td colspan="2">ASS 1122B CO</td><td>rev05</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2">Replace</td><td>SHEET</td></tr> </tbody> </table>							Scale	Free					Date	Name	Customer-No.	TOLERANCE		⑤	Add "USB 2.0 COMPLIANT"	19.08.2013	Amy	Drawn	04.05.2007	Hellwig	X.X	±0.3	④	Update	08.06.2013	Winnie	Approved	19.08.2013	Amy	X.XX	±0.20	③	Update	07.07.2009	Stefanie				X.XXX	±0.100	②	To adapt	11.09.2007	N.Schulz	ASSMANN WWS components			DIM	TOL	①	Production plant change	04.05.2007	Hellwing	ANG.	±1°					Angle	TOL	Id.	Modification	Date	Name	ASS 1122B CO		rev05							Replace		SHEET	H
Scale	Free					Date	Name	Customer-No.																																																																											
TOLERANCE		⑤	Add "USB 2.0 COMPLIANT"	19.08.2013	Amy	Drawn	04.05.2007	Hellwig																																																																											
X.X	±0.3	④	Update	08.06.2013	Winnie	Approved	19.08.2013	Amy																																																																											
X.XX	±0.20	③	Update	07.07.2009	Stefanie																																																																														
X.XXX	±0.100	②	To adapt	11.09.2007	N.Schulz	ASSMANN WWS components																																																																													
DIM	TOL	①	Production plant change	04.05.2007	Hellwing																																																																														
ANG.	±1°																																																																																		
Angle	TOL	Id.	Modification	Date	Name	ASS 1122B CO		rev05																																																																											
						Replace		SHEET																																																																											
	1	2	3	4	5	6	7	SV131																																																																											

NOTES:

- 1.Material:
- 1.1 Housing: PBT+30%GF UL94V-0, Color White
 - 1.2 Shell: Copper Alloy+
 - 1.3 Contact :Brass
2. FINISH:
- 2.1 Contact Area: Selective Gold Flash
 - Solder Area: Tin Plated
 - Under: Ni Plated
- 3.MECHANICAL:
- 3.1 Mating Force:3.57kgf Max.
 - 3.2 Unmating Force:1.02kgf Min
 - 3.3 Durability:1500 cycles Min
- 4.ELECTRICAL:
- 4.1 Current Rating:1.5A
 - 4.2 Dielectric Strength:500V AC FOR 1 MINUTE
 - 4.3 Contact Resistance:30mΩ Max
 - 4.4 Insulation Resistance:1000 MΩ Min
- 5.Operating temperature: -55°C TO +85°C
- 6.PACKIING: Tray

RECOMMENDED P.C.B LAYOUT

