



## Catalog No. TYB25MX

**Description:** CABLE TIE 50LB 7IN UV BLK NYL WKBOX

**UPC No** 5414363067146

**Home > Wire & Cable Management > Ty-Rap > Cable ties**

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (222 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 185.67mm (7.31 Inches), Width of 4.9mm (0.19 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Workbench Box Packaging

### Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

### Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 222 newtons

### Classifications

Brand Name	Ty-Rap
Standard	UL E49405

### Dimensions

Width	0.19 in , 4.9 mm
Length	7.2 in , 183 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.12 to 1.89 in , 3 to 48 mm

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant



ETIM	EC000046 Cable tie
Band width	4.9 mm
Length belt/tape/tie	361 mm
Length belt/tape/tie	14.2 inch
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	48 mm
Min. holding force	222 N
Operation temperature	-60-+105 °C
Operation temperature	-76-+221 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y