MJ14001 (PNP), MJ14002* (NPN), MJ14003* (PNP)

*Preferred Devices

High-Current Complementary Silicon Power Transistors

Designed for use in high−power amplifier and switching circuit applications.

Features

- High Current Capability − I_C Continuous = 60 Amperes
- DC Current Gain − h_{FE} = 15 − 100 @ I_C = 50 Adc
- Low Collector−Emitter Saturation Voltage −$V_{CE(sat)}$ = 2.5 Vdc (Max) @ I_C = 50 Adc
- Pb−Free Packages are Available*

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Rating		Symbol	Value	Unit
Collector−Emitter Voltage	MJ14001 MJ14002/03	V_{CEO}	60 80	Vdc
Collector−Base Voltage	MJ14001 MJ14002/03	V_{CBO}	60 80	Vdc
Emitter−Base Voltage		V_{EBO}	5.0	Vdc
Collector Current − Continuous		I_C	60	Adc
Base Current − Continuous		I_B	15	Adc
Emitter Current − Continuous		I_E	75	Adc
Total Power Dissipation @ T_C = 25°C Derate Above 25°C		P_D	300 1.71	W W/°C
Operating and Storage Junction Temperature Range		T_J, T_{stg}	−65 to +200	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.





Figure 1. Power Derating

ON Semiconductor®

http://onsemi.com

60 AMPERE COMPLEMENTARY SILICON POWER TRANSISTORS 60−80 VOLTS, 300 WATTS

MARKING DIAGRAM





TO−204 (TO−3)
CASE 197A−05
STYLE 1

MJ1400x = Device Code
xx = 1, 2, or 3
G = Pb−Free Package
A = Location Code
YY = Year
WW = Work Week
MEX = Country of Orgin

ORDERING INFORMATION

Device	Package	Shipping
MJ14001	TO−3	100 Units/Tray
MJ14001G	TO−3 (Pb−Free)	100 Units/Tray
MJ14002	TO−3	100 Units/Tray
MJ14002G	TO−3 (Pb−Free)	100 Units/Tray
MJ14003	TO−3	100 Units/Tray
MJ14003G	TO−3 (Pb−Free)	100 Units/Tray

Preferred devices are recommended choices for future use and best overall value.

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DISCONTINUED
THIS DEVICE IS NOT AVAILABLE
PLEASE CONTACT YOUR onsemi
REPRESENTATIVE FOR INFORMATION

© Semiconductor Components Industries, LLC, 2005

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction−to−Case	$R_{\theta JC}$	0.584	°C/W

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Max	Unit
OFF CHARACTERISTICS					
Collector−Emitter Sustaining Voltage (Note 1)		$V_{CEO(sus)}$			Vdc
(I_C = 200 mAdc, I_B = 0)	MJ14001		60	–	
	MJ14002, MJ14003		80	–	
Collector Cutoff Current		I_{CEO}			mA
(V_{CE} = 30 Vdc, I_B = 0)	MJ14001		–	1.0	
(V_{CE} = 40 Vdc, I_B = 0)	MJ14402, MJ14003		–	1.0	
Collector Cutoff Current		I_{CEX}			mA
(V_{CE} = 60 Vdc, $V_{BE(off)}$ = 1.5 V)	MJ14001		–	1.0	
(V_{CE} = 80 Vdc, $V_{BE(off)}$ = 1.5 V)	MJ14002, MJ14003		–	1.0	
Collector Cutoff Current		I_{CBO}			mA
(V_{CB} = 60 Vdc, I_E = 0)	MJ14001		–	1.0	
(V_{CB} = 80 Vdc, I_E = 0)	MJ14002, MJ14003		–	1.0	
Emitter Cutoff Current		I_{EBO}	–	1.0	mA
(V_{BE} = 5.0 Vdc, I_C = 0)					
ON CHARACTERISTICS					
DC Current Gain (Note 1)		h_{FE}			–
(I_C = 25 Adc, V_{CE} = 3.0 V)			30	–	
(I_C = 50 Adc, V_{CE} = 3.0 V)			15	100	
(I_C = 60 Adc, V_{CE} = 3.0 V)			5.0	–	
Collector−Emitter Saturation Voltage (Note 1)		$V_{CE(sat)}$			Vdc
(I_C = 25 Adc, I_B = 2.5 Adc)			–	1.0	
(I_C = 50 Adc, I_B = 5.0 Adc)			–	2.5	
(I_C = 60 Adc, I_B = 12 Adc)			–	3.0	
Base−Emitter Saturation Voltage (Note 1)		$V_{BE(sat)}$			Vdc
(I_C = 25 Adc, I_B = 2.5 Adc)			–	2.0	
(I_C = 50 Adc, I_B = 5.0 Adc)			–	3.0	
(I_C = 60 Adc, I_B = 12 Adc)			–	4.0	
DYNAMIC CHARACTERISTICS					
Output Capacitance		C_{ob}	–	2000	pF
(V_{CB} = 10 Vdc, I_E = 0, f = 0.1 MHz)					

1. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2.0%.

PLEASE REFER TO REPRESENTATIVE




Figure 2. Maximum Rated Forward Biased Safe Operating Area

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation: i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 2 is based on $T_{J(pk)}$ = 200°C; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(pk)}$ ≤ 200°C. $T_{J(pk)}$ may be calculated from the data in Figure 13. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.

Downloaded from Arrow.com.

TYPICAL ELECTRICAL CHARACTERISTICS

MJ14002 (NPN)




Figure 3. DC Current Gain

MJ14001, MJ14003 (PNP)




Figure 4. DC Current Gain




Figure 5. Collector Saturation Region




Figure 6. Collector Saturation Region




Figure 7. “On” Voltages




Figure 8. “On” Voltages

DISCONTINUED
THIS DEVICE IS NOT AVAILABLE
PLEASE CONTACT YOUR onsemi
REPRESENTATIVE FOR INFORMATION

Downloaded from Arrow.com.




Figure 9. Turn−On Switching Times




Figure 10. Turn−Off Switching Times





Figure 11. Capacitance Variation



FOR CURVES OF FIGURES 3 & 6, R_B & R_L ARE VARIED.
INPUT LEVELS ARE APPROXIMATELY AS SHOWN.
FOR NPN CIRCUITS, REVERSE ALL POLARITIES.

Figure 12. Switching Test Circuit




Figure 13. Thermal Response

DISCONTINUED
THIS DEVICE IS NOT AVAILABLE
PLEASE CONTACT YOUR onsemi
REPRESENTATIVE FOR INFORMATION

Downloaded from Arrow.com.


REVISION HISTORY

Revision	Description of Changes	Date
7	Data Sheet Discontinued.	1/15/2026

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

DISCONTINUED
THIS DEVICE IS NOT AVAILABLE
PLEASE CONTACT YOUR onsemi
REPRESENTATIVE FOR INFORMATION


Downloaded from Arrow.com.




SCALE 1:1

TO−204 (TO−3)
CASE 197A−05
ISSUE K

DATE 21 FEB 2000





NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	1.530 REF		38.86 REF	
B	0.990	1.050	25.15	26.67
C	0.250	0.335	6.35	8.51
D	0.057	0.063	1.45	1.60
E	0.060	0.070	1.53	1.77
G	0.430 BSC		10.92 BSC	
H	0.215 BSC		5.46 BSC	
K	0.440	0.480	11.18	12.19
L	0.665 BSC		16.89 BSC	
N	0.760	0.830	19.31	21.08
Q	0.151	0.165	3.84	4.19
U	1.187 BSC		30.15 BSC	
V	0.131	0.188	3.33	4.77


STYLE 1:
PIN 1. BASE
2. EMITTER
CASE: COLLECTOR

STYLE 2:
PIN 1. EMITTER
2. BASE
CASE: COLLECTOR

STYLE 3:
PIN 1. GATE
2. SOURCE
CASE: DRAIN

STYLE 4:
PIN 1. ANODE = 1
2. ANODE = 2
CASE: CATHODES

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code
A = Assembly Locationa
YY = Year
WW = Work Week

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98ASB42129B**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−204 (TO−3)**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.