



Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER			
51939-307-- NOTE 3	D C B A	E1	P1	P2	E2
			PA	PA	



VIEW D-D



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
HA	[N/A]	HOLD-DOWN

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER	FCI	
litr	ecn no.	dr	date			linear	0.X ±0.3	COPY	www.fciconnect.com	
A	DG07-0437	JMG	07/10/07				0.XX ±0.13	projection	title	
						angles	0.XXX ±0.051		IP + 4S + IP	
						dr	0° ±2°	MIM	RIGHT ANGLE SOLDER HEADER	
						enr	JM GUO 07/10/07	scale	product family	PwrBlade
						chr	JEROME CHEN 07/10/07	1:1	size	code
						appd	GARY HSIEH 07/10/07		dwg no	213
							JOSEPH HSIA 07/10/07		51939-307	sheet
sheet index	revision sheet	A	A	A	A					1 of 4
		1	2	3	4					

cage code 22526


Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-307_-
NOTE: 3



BROKEN-OUT SECTION A-A
SCALE 2:1



BROKEN-OUT SECTION B-B
SCALE 2:1

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A				linear		0.X ±0.3		projection		title	IP + 4S + IP
						0.XX ±0.13					RIGHT ANGLE SOLDER HEADER
				angles		0.XXX ±0.051				product family	PwrBlade
				dr	JM GUO	07/10/07				code	213
				enr	JEROME CHEN	07/10/07				size	dwg no
				chr	GARY HSIEH	07/10/07				A	51939-307
				appd	JOSEPH HSIA	07/10/07				sheet	2 of 4
sheet index	revision sheet							scale	1:1		

cage code 22526


Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-307_
NOTE: 3



RECOMMENDED PCB LAYOUT

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A				linear		0.X ±0.3		projection		title	
						0.XX ±0.13				IP + 4S + IP	
				angles		0.XXX ±0.051				RIGHT ANGLE SOLDER HEADER	
				dr	JM GUO	07/10/07		MIM		product family	PwrBlade
				enrg	JEROME CHEN	07/10/07		scale		size	code
				chr	GARY HSIEH	07/10/07		1:1		dwg no	213
				appd	JOSEPH HSIA	07/10/07				51939-307	sheet
sheet index	revision sheet										3 of 4

cage code 22526

Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-307_- NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. 51939-307; 51939-307LF PLATING SPEC. SEE PRINT:10064183
4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
9. $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
11. CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE				tolerances unless otherwise specified				CUSTOMER								www.fciconnect.com			
litr		ecn no.		dr		date		linear		0.X ± 0.3		COPY				title IP + 4S + IP RIGHT ANGLE SOLDER HEADER		product family PwrBlade		code 213			
A						0.XX ± 0.13				projection													
						0.XXX ± 0.051																	
								angles		0° ± 2°													
				dr		JM GUO		07/10/07															
				enrg		JEROME CHEN		07/10/07				scale											
				chr		GARY HSIEH		07/10/07															
				appd		JOSEPH HSIA		07/10/07				1:1											
sheet		revision																					
index		sheet																					

cage code 22526