



Color: ■ orange

Physical data		
Width		1 mm / 0.039 inches
Height		65 mm / 2.56 inches
Depth		29.7 mm / 1.169 inches

Mechanical data	
Mounting type	snap-on type

Material data		
Note (material data)		Information on material specifications can be found here
Color		orange
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.056 MJ
Weight		2.1 g

Environmental requirements		
Processing temperature	-35 ... +85 °C	Environmental Testing Test specification: Railway applications – Rolling stock – Electronic equipment DIN EN 50155 (VDE 0115-200):2022-06 Test procedure: Railway applications – Rolling stock equipment – Vibration and shock tests DIN EN 61373 (VDE 0115-0106):2011-04 Spectrum/Mounting location Service life test, Category 1, Class A/B Functional test with noise-like oscillations Test passed according to Section 8 of the standard Frequency f₁ = 5 Hz to f₂ = 150 Hz
Continuous operating temperature	-60 ... +105 °C	



Environmental Testing	
Acceleration	0.101g (highest test level used for all axes)
Test duration per axis	10 min.
Test directions	X, Y and Z axes
Monitoring of contact faults and interruptions	Passed
Voltage drop measurement before and after each axis	Passed
Simulated service life test through increased levels of noise-like oscillations	Test passed according to Section 9 of the standard
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
Acceleration	0.572g (highest test level used for all axes)
Test duration per axis	5 h
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Shock test	Test passed according to Section 10 of the standard
Shock pulse form	Half sine
Acceleration	5g (highest test level used for all axes)
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed

Commercial data	
Product Group	22 (TOPJOB S)
PU (SPU)	100 (25) pcs
Packaging type	Box
Country of origin	CN
GTIN	4044918451826
Customs tariff number	85389099990

Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates

Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 2004-1392

↓

Documentation			
Bid Text			
2004-1392	28.04.2017	doc 23.50 KB	↓
2004-1392	19.02.2019	xml 2.51 KB	↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 2004-1392	EPLAN Data Portal 2004-1392
	WSCAD Universe 2004-1392
	ZUKEN Portal 2004-1392

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com