

# MOSFET - N-Channel, POWERTRENCH®

30 V, 13.2 A, 9.5 mΩ

## FDMS7694, FDMS7694-NC

### General Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency and to minimize switch node ringing of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low  $R_{DS(on)}$ , fast switching speed and body diode reverse recovery performance.


### Features

- Max  $R_{DS(on)}$  = 9.5 mΩ at  $V_{GS}$  = 10 V,  $I_D$  = 13.2 A
- Max  $R_{DS(on)}$  = 14.5 mΩ at  $V_{GS}$  = 4.5 V,  $I_D$  = 10.5 A
- Advanced Package and Silicon Combination for Low  $R_{DS(on)}$  and High Efficiency
- Next Generation Enhanced Body Diode Technology, Engineered for Soft Recovery
- MSL1 Robust Package Design
- 100% UIL Tested
- This Device is Halide Free and RoHS Compliant with Exemption 7a, Pb-Free 2LI (on second level interconnection)

### Applications


- IMVP Vcore Switching for Notebook
- VRM Vcore Switching for Desktop and Server
- OringFET / Load Switching
- DC-DC Conversion

| $V_{DS}$ | $R_{DS(on)}$ MAX           | $I_D$ Max |
|----------|----------------------------|-----------|
| 30 V     | 14.5 mΩ @ $V_{GS}$ = 4.5 V | 10.5 A    |
|          | 9.5 mΩ @ $V_{GS}$ = 10 V   | 13.2 A    |




PQFN8 5X6, 1.27P  
Power 56  
CASE 483AE

### MARKING DIAGRAM



&Z = Assembly Plant Code  
& = 3-Digit Date Code  
&K = 2-Digits Lot Run Code  
FDMS7694 = Specific Device Code

### PIN CONNECTIONS



### ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

# FDMS7694, FDMS7694-NC

## MAXIMUM RATINGS (T<sub>A</sub> = 25 °C unless otherwise noted)

| Symbol                            | Parameter                                        |                                                      | Rating      | Unit |
|-----------------------------------|--------------------------------------------------|------------------------------------------------------|-------------|------|
| V <sub>DS</sub>                   | Drain to Source Voltage                          |                                                      | 30          | V    |
| V <sub>GS</sub>                   | Gate to Source Voltage (Note 3)                  |                                                      | ±20         | V    |
| I <sub>D</sub>                    | Drain Current                                    | Continuous (Package Limited), T <sub>C</sub> = 25 °C | 20          | A    |
|                                   |                                                  | Continuous (Silicon Limited), T <sub>C</sub> = 25 °C | 44          |      |
|                                   |                                                  | Continuous, T <sub>A</sub> = 25 °C (Note 1a)         | 13.2        |      |
|                                   |                                                  | Pulsed                                               | 50          |      |
| E <sub>AS</sub>                   | Single Pulse Avalanche Energy (Note 4)           |                                                      | 21          | mJ   |
| P <sub>D</sub>                    | Power Dissipation                                | T <sub>C</sub> = 25 °C                               | 27          | W    |
|                                   |                                                  | T <sub>A</sub> = 25 °C (Note 1a)                     | 2.5         |      |
| T <sub>J</sub> , T <sub>STG</sub> | Operating and Storage Junction Temperature Range |                                                      | –55 to +150 | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

## THERMAL CHARACTERISTICS

| Symbol           | Parameter                                         | Rating | Unit |
|------------------|---------------------------------------------------|--------|------|
| R <sub>θJC</sub> | Thermal Resistance, Junction-to-Case              | 4.5    | °C/W |
| R <sub>θJA</sub> | Thermal Resistance, Junction-to-Ambient (Note 1a) | 50     |      |

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25 °C unless otherwise noted)

| Symbol | Parameter | Test Condition | Min | Typ | Max | Unit |
|--------|-----------|----------------|-----|-----|-----|------|
|--------|-----------|----------------|-----|-----|-----|------|

### OFF CHARACTERISTICS

|                                      |                                           |                                                |    |    |     |       |
|--------------------------------------|-------------------------------------------|------------------------------------------------|----|----|-----|-------|
| BV <sub>DSS</sub>                    | Drain-to-Source Breakdown Voltage         | I <sub>D</sub> = 250 μA, V <sub>GS</sub> = 0 V | 30 |    |     | V     |
| $\frac{\Delta BV_{DSS}}{\Delta T_J}$ | Breakdown Voltage Temperature Coefficient | I <sub>D</sub> = 250 μA, referenced to 25 °C   |    | 16 |     | mV/°C |
| I <sub>DSS</sub>                     | Zero Gate Voltage Drain Current           | V <sub>DS</sub> = 24 V, V <sub>GS</sub> = 0 V  |    |    | 1   | μA    |
| I <sub>GSS</sub>                     | Gate-to-Source Leakage Current, Forward   | V <sub>GS</sub> = 20 V, V <sub>DS</sub> = 0 V  |    |    | 100 | nA    |

### ON CHARACTERISTICS

|                                        |                                                          |                                                                          |     |      |      |       |
|----------------------------------------|----------------------------------------------------------|--------------------------------------------------------------------------|-----|------|------|-------|
| V <sub>GS(th)</sub>                    | Gate-to-Source Threshold Voltage                         | V <sub>GS</sub> = V <sub>DS</sub> , I <sub>D</sub> = 250 μA              | 1.0 | 2.0  | 3.0  | V     |
| $\frac{\Delta V_{GS(th)}}{\Delta T_J}$ | Gate-to-Source Threshold Voltage Temperature Coefficient | I <sub>D</sub> = 250 μA, referenced to 25 °C                             |     | –6   |      | mV/°C |
| R <sub>DS(on)</sub>                    | Static Drain-to-Source On Resistance                     | V <sub>GS</sub> = 10 V, I <sub>D</sub> = 13.2 A                          |     | 7.6  | 9.5  | mΩ    |
|                                        |                                                          | V <sub>GS</sub> = 4.5 V, I <sub>D</sub> = 10.5 A                         |     | 11.1 | 14.5 |       |
|                                        |                                                          | V <sub>GS</sub> = 10 V, I <sub>D</sub> = 13.2 A, T <sub>J</sub> = 125 °C |     | 10.6 | 13.3 |       |
| g <sub>FS</sub>                        | Forward Transconductance                                 | V <sub>DS</sub> = 5 V, I <sub>D</sub> = 13.2 A                           |     | 55   |      | S     |

### DYNAMIC CHARACTERISTICS

|                  |                              |                                                          |  |      |      |    |
|------------------|------------------------------|----------------------------------------------------------|--|------|------|----|
| C <sub>iss</sub> | Input Capacitance            | V <sub>DS</sub> = 15 V, V <sub>GS</sub> = 0 V, f = 1 MHz |  | 1060 | 1410 | pF |
| C <sub>oss</sub> | Output Capacitance           |                                                          |  | 353  | 470  | pF |
| C <sub>rss</sub> | Reverse Transfer Capacitance |                                                          |  | 36   | 55   | pF |
| R <sub>g</sub>   | Gate Resistance              |                                                          |  | 0.8  | 1.6  | Ω  |

# FDMS7694, FDMS7694-NC

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)


| Symbol                           | Parameter                     | Test Condition                                                                                  | Min | Typ | Max | Unit |
|----------------------------------|-------------------------------|-------------------------------------------------------------------------------------------------|-----|-----|-----|------|
| <b>SWITCHING CHARACTERISTICS</b> |                               |                                                                                                 |     |     |     |      |
| $t_{d(on)}$                      | Turn-On Delay Time            | $V_{DD} = 15\text{ V}$ , $I_D = 13.2\text{ A}$ , $V_{GS} = 10\text{ V}$ , $R_{GEN} = 6\ \Omega$ |     | 8.4 | 17  | ns   |
| $t_r$                            | Rise Time                     |                                                                                                 |     | 2   | 10  | ns   |
| $t_{d(off)}$                     | Turn-Off Delay Time           |                                                                                                 |     | 18  | 33  | ns   |
| $t_f$                            | Fall Time                     |                                                                                                 |     | 1.6 | 10  | ns   |
| $Q_{g(TOT)}$                     | Total Gate Charge             | $V_{GS} = 0\text{ V to }10\text{ V}$ , $V_{DD} = 15\text{ V}$ , $I_D = 13.2\text{ A}$           |     | 15  | 22  | nC   |
|                                  | Total Gate Charge             | $V_{GS} = 0\text{ V to }4.5\text{ V}$ , $V_{DD} = 15\text{ V}$ , $I_D = 13.2\text{ A}$          |     | 7   | 10  | nC   |
| $Q_{gs}$                         | Gate-to-Source Charge         | $V_{DD} = 15\text{ V}$ , $I_D = 13.2\text{ A}$                                                  |     | 3.3 |     | nC   |
| $Q_{gd}$                         | Gate-to-Drain "Miller" Charge |                                                                                                 |     | 2.0 |     | nC   |

## DRAIN-SOURCE DIODE CHARACTERISTICS


|          |                                       |                                                            |  |      |     |    |
|----------|---------------------------------------|------------------------------------------------------------|--|------|-----|----|
| $V_{SD}$ | Source to Drain Diode Forward Voltage | $V_{GS} = 0\text{ V}$ , $I_S = 2.1\text{ A}$ (Note 2)      |  | 0.76 | 1.1 | V  |
|          |                                       | $V_{GS} = 0\text{ V}$ , $I_S = 13.2\text{ A}$ (Note 2)     |  | 0.85 | 1.1 |    |
| $t_{rr}$ | Reverse Recovery Time                 | $I_F = 13.2\text{ A}$ , $di/dt = 100\text{ A}/\mu\text{s}$ |  | 23   | 37  | ns |
| $Q_{rr}$ | Reverse Recovery Charge               |                                                            |  | 7    | 14  | nC |
| $t_{rr}$ | Reverse Recovery Time                 | $I_F = 13.2\text{ A}$ , $di/dt = 300\text{ A}/\mu\text{s}$ |  | 18   | 33  | ns |
| $Q_{rr}$ | Reverse Recovery Charge               |                                                            |  | 14   | 26  | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- $R_{\theta JA}$  is determined with the device mounted on a 1 in<sup>2</sup> pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a.  $50^\circ\text{C/W}$  when mounted on a 1 in<sup>2</sup> pad of 2 oz copper.



b.  $125^\circ\text{C/W}$  when mounted on a minimum pad of 2 oz copper.

- Pulse Test: Pulse Width < 300  $\mu\text{s}$ , Duty cycle < 2.0%.
- $E_{AS}$  of 21 mJ is based on starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.3\text{ mH}$ ,  $I_{AS} = 12\text{ A}$ ,  $V_{DD} = 27\text{ V}$ ,  $V_{GS} = 10\text{ V}$ . 100% test at  $L = 0.1\text{ mH}$ ,  $I_{AS} = 20\text{ A}$ .
- As an N-ch device, the negative  $V_{GS}$  rating is for low duty cycle pulse occurrence only. No continuous rating is implied.



TYPICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$  unless otherwise noted)




Figure 1. On Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source-to-Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$  unless otherwise noted) (continued)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

# FDMS7694, FDMS7694-NC

## TYPICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)




Figure 13. Junction-to-Ambient Transient Thermal Response Curve

### PACKAGE MARKING AND ORDERING INFORMATION

| Device      | Device Marking | Package Type                 | Reel Size | Tape Width | Shipping <sup>†</sup> |
|-------------|----------------|------------------------------|-----------|------------|-----------------------|
| FDMS7694    | FDMS7694       | PQFN8 5X6, 1.27P<br>Power 56 | 13"       | 12 mm      | 3000 / Tape & Reel    |
| FDMS7694-NC |                |                              |           |            |                       |

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.


## FDMS7694, FDMS7694-NC

### REVISION HISTORY


| Revision | Description of Changes                                         | Date      |
|----------|----------------------------------------------------------------|-----------|
| 4        | Converted the document to <b>onsemi</b> format. Added new OPN. | 6/19/2026 |

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.





**PQFN8 5X6, 1.27P**  
**CASE 483AE**  
**ISSUE C**

DATE 21 JAN 2022




TOP VIEW





OPTIONAL DRAFT  
ANGLE MAY APPEAR  
ON FOUR SIDES  
OF THE PACKAGE

## NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.
6. IT IS RECOMMENDED TO HAVE NO TRACES OR VIAS WITHIN THE KEEP OUT AREA.



SIDE VIEW


DETAIL C  
SCALE: 2:1

DETAIL B  
SCALE: 2:1


BOTTOM VIEW


LAND PATTERN  
RECOMMENDATION

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERM/D.

| DIM | MILLIMETERS |      |      |
|-----|-------------|------|------|
|     | MIN.        | NOM. | MAX. |
| A   | 0.90        | 1.00 | 1.10 |
| A1  | 0.00        | -    | 0.05 |
| b   | 0.21        | 0.31 | 0.41 |
| b1  | 0.31        | 0.41 | 0.51 |
| A3  | 0.15        | 0.25 | 0.35 |
| D   | 4.90        | 5.00 | 5.20 |
| D1  | 4.80        | 4.90 | 5.00 |
| D2  | 3.61        | 3.82 | 3.96 |
| E   | 5.90        | 6.15 | 6.25 |
| E1  | 5.70        | 5.80 | 5.90 |
| E2  | 3.38        | 3.48 | 3.78 |
| E3  | 0.30 REF    |      |      |
| E4  | 0.52 REF    |      |      |
| e   | 1.27 BSC    |      |      |
| e/2 | 0.635 BSC   |      |      |
| e1  | 3.81 BSC    |      |      |
| e2  | 0.50 REF    |      |      |
| L   | 0.51        | 0.66 | 0.76 |
| L2  | 0.05        | 0.18 | 0.30 |
| L4  | 0.34        | 0.44 | 0.54 |
| z   | 0.34 REF    |      |      |
| Θ   | 0°          | -    | 12°  |

DOCUMENT NUMBER: 98AON13655G

Electronic versions are uncontrolled except when accessed directly from the Document Repository.  
Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

DESCRIPTION: PQFN8 5X6, 1.27P

PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

