Part Number : 398900604
Product Description : 5.00mm Pitch Beau Eurostyle Medium Profile, Two Level Terminal Block, Modular, 4 Circuits
Series Number : 39890
Status : Active
Product Category : Terminal Blocks and Barrier Strip
Engineering Part Number : MX-PSM020D1-0N



Documents and Resources

Drawings

398900604_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39890
Description	5.00mm Pitch Beau Eurostyle Medium Profile, Two Level Terminal Block, Modular, 4 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Multi-Level
Type	PCB Terminal Blocks and Connectors
UPC	800753317420

Agency

UL	E48521

Electrical

Current - Maximum per Contact	17.5A
Voltage - Maximum	150V

Physical

Circuits (Loaded)	4

Downloaded from Arrow.com.

Circuits (maximum)	4
Color - Resin	Black
Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	No
Net Weight	1.000/g
Number of Rows	2
Orientation	Vertical
Panel Mount	No
PCB Retention	N/A
PCB Thickness - Recommended	2.60mm
PC Tail Length	3.81mm
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	No
Shrouded	Shrouded
Stackable	Yes
Temperature Range - Operating	105°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm^2	0.20-2.50

Downloaded from Arrow.com.