# Data sheet

## DRR273024L

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

### Product image



Similar to illustration

Individual relays within the D-SERIES DRR
- 2 CO contacts
- Optional AC or DC coils
- With integrated status LED

### General ordering data

| | |
|---|---|
| Version | D-SERIES DRR, Relay, Number of contacts: 2, CO contact AgSnO, Rated control voltage: 24 V DC, Continuous current: 10 A, Plug-in connection, Test button available: No |
| Order No. | 2765020000 |
| Type | DRR273024L |
| GTIN (EAN) | 4064675077176 |
| Qty. | 10 items |



Downloaded from Arrow.com.

# Data sheet

## DRR273024L

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E312083 |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 66 mm | Depth (inches) | 2.5984 inch |
| Height | 34.5 mm | Height (inches) | 1.3583 inch |
| Width | 34.5 mm | Width (inches) | 1.3583 inch |
| Net weight | 81.6 g | | |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -25 °C...55 °C |
| Operating temperature | | Humidity | 5...85 % rel. humidity, no condensation |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### Rated data UL

| | |
|---|---|
| Certificate No. (cURus) | E312083 |

### Control side

| | | | |
|---|---|---|---|
| Rated control voltage | 24 V DC | Rated current DC | 55.8 mA |
| Power rating | 1.5 W | Coil resistance | 430 Ω ± 10 % |
| Status indicator | Green LED | | |

### Load side

| | | | |
|---|---|---|---|
| Rated switching voltage | 250 V AC | Continuous current | 10 A |
| Max. switching frequency at rated load | 0.1 Hz | Max. switching voltage, AC | 250 V |
| Inrush current | 50 A / 50 ms | AC switching capacity (resistive), max. | 2500 VA |
| DC switching capacity (resistive), max. | 240 W @ 24 V | Switch-on delay | <30 ms |
| Switch-off delay | <20 ms | Contact type | 2 CO contact (AgSnO) |
| Mechanical service life | 10 x 106 switching cycles | Min. switching power | 10 mA @ 12 V |

### General data

| | | |
|---|---|---|
| Test button available | No | |
| Mechanical switch position indicator | Yes | |
| Colour | Transparent | |
| UL94 flammability rating component | Component | Relay status indicator |
| | UL94 flammability rating | HB |
| | Component | Relay baseplate |
| | UL94 flammability rating | V-0 |
| | Component | Relay cover |
| | UL94 flammability rating | V-2 |



Downloaded from Arrow.com.

Weidmüller

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

## Insulation coordination

| | | | |
|---|---|---|---|
| Rated voltage | 250 V | Pollution severity | 3 |
| Surge voltage category | III | Insulating material group | IIIa |
| Clearance and creepage distances for control side - load side | ≥ 4 mm | Dielectric strength for control side - load side | 2.5 kVeff / 1 Min. |
| Dielectric strength of neighbouring contacts | 2.5 kVeff / 1 Min. | Dielectric strength of open contact | 1.2 kVeff /1 min. |
| Impulse withstand voltage | 4 kV (1.2/50 µs) | Protection degree | IP20 |

## Further details of approvals / standards

| | |
|---|---|
| Certificate No. (cURus) | E312083 |

## Connection data

| | |
|---|---|
| Wire connection method | Plug-in connection |

## Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001437 | ETIM 9.0 | EC001437 |
| ETIM 10.0 | EC001437 | ECLASS 14.0 | 27-37-16-01 |
| ECLASS 15.0 | 27-37-16-01 | | |



Downloaded from Arrow.com.


Weidmüller

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


# Drawings

## Wiring diagram





View of Pins from below

## Graph





DC load limit curve Resistive load

## Graph





Electrical service life

## Graph




DC operational voltage range

## Dimensional drawing







Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### Miscellaneous




Type codes



Downloaded from Arrow.com.