

Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, lettering field size: 7 x 10 mm, Number of individual labels: 30

Your advantages

- UniCard snap-in device marking for Axioline E series.
- The markers, which are supplied in uniform sheets, can be marked quickly and easily using the BLUEMARK CLED and the THERMOMARK CARD.
- The wide temperature range means that the labels can be used in control cabinets as well as the field

Snap-in markers - UCT-EM (7X10)



0830765

<https://www.phoenixcontact.com/us/products/0830765>

Commercial Data

Item number	0830765
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B12
Product Key	BG2418
Catalog Page	Page 306 (C-3-2019)
GTIN	4046356745574
Weight per Piece (including packing)	10.35 g
Weight per Piece (excluding packing)	9 g
Customs tariff number	39269097
Country of origin	PL

Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Technical Data

Product properties

Product type	Device marking
Marking	
Number of individual labels	30
Number of individual labels per row	6

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Mounting

Mounting type	snapped
---------------	---------

Material specifications

Color	white
RoHS compliant	Yes
Material	PC
Flammability rating according to UL 94	V0
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium
Silicone-free	Yes
Halogen-free	Yes

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed

Snap-in markers - UCT-EM (7X10)



0830765

<https://www.phoenixcontact.com/us/products/0830765>

Climate level	AHT 1,0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Dimensions

Width	7 mm
Length	10 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Classifications

ECLASS

ECLASS-9.0	27400629
ECLASS-10.0.1	27400629
ECLASS-11.0	27281103

ETIM

ETIM 8.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Accessories

Magazine

Magazine - THERMOMARK CARD-UCT-MAG7 - 0801734

<https://www.phoenixcontact.com/us/products/0801734>

Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-WMT...)



Magazine

Magazine - TMP-UCT-MAG7 - 0803349

<https://www.phoenixcontact.com/us/products/0803349>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMT..., UCT-EM (7x10)



Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>




Magazine

Magazine - TOPMARK LASER-MAG UCT-A - 0803141

<https://www.phoenixcontact.com/us/products/0803141>

Magazine for the TOPMARK LASER, for accommodating UCT material automatically



Magazine

Magazine - TOPMARK LASER-MAG UCT-M - 0803143

<https://www.phoenixcontact.com/us/products/0803143>

Magazine for the TOPMARK LASER, for accommodating UCT material manually



Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BK 100 - 0803374

<https://www.phoenixcontact.com/us/products/0803374>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., width: 110 mm, color: black

Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Ink cartridge

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



Ink cartridge

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110/50-TC - 0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

Snap-in markers - UCT-EM (7X10)

0830765

<https://www.phoenixcontact.com/us/products/0830765>



Ink cartridge

Ink cartridge - BM ID-CARTR. CY - 1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

Ink cartridge

Ink cartridge - BM ID-CARTR. YE - 1044348

<https://www.phoenixcontact.com/us/products/1044348>



Replacement UV fluid, 23 ml, color: yellow

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com