



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 125 °C [257 °F]

Pre-Installed Lead: No

Features

Product Type Features

Temperature Indicator	Yes
Temperature Indicator Type	Thermochromic

Configuration Features

Pre-Installed Lead	No
--------------------	----

Dimensions

Compatible Jacket Diameter Range	2 mm[.08 in]
Product Length	16 mm[.63 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Industry Standards

Government Qualified	No
----------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # EG8162-000
HL1920E-230V-EURO

Customers Also Bought

TE Part #EH3263-000
ZH150-5/2.5-0-SP

TE Part #620004-000
D-103-00

TE Part #3970213001
100G0111-0.60-0

TE Part #796864-3
3 POS TERMI-BLOK HDR RT ANGLE

TE Part #966067-3
FER,WIRE,PL SLV,.50/20,L10,WHITE,LP

TE Part #4-1437221-3
FSK-22A

TE Part #1676402-2
RN 0805 64K9 0.1% 10PPM 1KRL

TE Part #5206052-3
SCREW,SPECIAL,ZN



Documents

Product Drawings

CWT-1501

English

Datasheets & Catalog Pages

1654025_Sec8_B-155_CWT_D-110_D-1744

English

Product Specifications

SolderSleeve One-Step Wire and Cable Terminators Installation Procedures for CWT and B-155 Products

English