


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:

1. SEE CURRENT CATALOG TO INDICATE PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PRODUCT DESCRIPTION:
 - A. 1 LANE, 25 Gbps/LANE
 - B. STANDARD SFP CONNECTOR
 - C. CL2 RATED JACKET
 - D. JACKET COLOR: BLACK (BL)
4. MATES WITH SFP SFF-8432 INTERFACE
5. CABLE LABEL CONTAINS PRODUCT DESCRIPTION, PART NUMBER, LENGTH AND WIRE GAUGE, AND MANUFACTURING SERIAL NUMBER.

TABLE 1
CABLE ASSEMBLY

PART NUMBER	LENGTH METERS (+.15, -0)	LENGTH FEET (+.5, -0)	CABLE AWG	WEIGHT LBS
PSF2PXA1M**	1	3.3	30	0.13
PSF2PXA2M**	2	6.6	30	0.19
PSF2PXA3M**	3	9.8	30	0.24
PSF2PXD4M**	4	13.1	24	0.49
PSF2PXD5M**	5	16.4	24	0.60

**CABLE COLOR IN BLACK (BL)



PART NUMBER SEE TABLE 1		PRODUCT SPEC/PKG SPEC N/A	
I.T. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE SFP28 PASSIVE CABLE ASSEMBLY			
CUSTOMER DRAWING			
ITEM REVISION NAME M03075MQ/00		PANDUIT	
DATASET FILE NAME M03075MQ_DC216/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL:	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 03075-216	
DRAWN BY BJN	DATE 11-19-15	CHK JAV	SCALE NONE
SHT 1 OF 2		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	11-30-15	BJN	JAV	DFP	RELEASED TO PRODUCTION	03075-216

